



Product: [81553](#)

77Ω Twinax, #24 SCHSCA, TFE, SCHSCA Braid, PFA Jkt

Product Description

Twinax, 77 ohm, 24 AWG stranded (19x36) .024" silver-coated high-strength copper alloy conductor, TFE insulation, silver-coated high strength copper alloy braid shield (93% coverage), PFA jacket, commercial non-QPL product

Technical Specifications

Product Overview

Suitable Applications: Harsh Environment, IIoT, Factory or Process Automation, Video, Audio, Data Communication, etc.

Construction Details

Conductor

No. of Elements	Size	Stranding	Nom. Diameter	Material
2	24 AWG	19x36	0.024 in	SHSCA - Silver Coated High Strength Copper Alloy

Insulation

Material	Nom. Insulation Diameter	Color Code
PTFE - Polytetrafluoroethylene	0.042 in (1.1 mm)	White & Blue

Outer Shield

Outer Shield Type	Material	Coverage
Braid	Silvered High Strength Copper Alloy (SHSCA)	93%

Outer Jacket

Material	Nom. Diameter
PFA - Perfluoroalkoxy	0.129 in (3.28 mm)

Electrical Characteristics

Attenuation

Frequency	Nom. Attenuation
1 MHz	1.2 dB/100ft
10 MHz	4.0 dB/100ft
50 MHz	9.2 dB/100ft
100 MHz	13.0 dB/100ft
200 MHz	18.4 dB/100ft
400 MHz	26.1 dB/100ft
700 MHz	34.6 dB/100ft
900 MHz	39.3 dB/100ft
1000 MHz	41.4 dB/100ft

Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.	Max. Delay Skew
24.5 Ohm/1000ft	7.3 Ohm/1000ft (24 Ohm/km)	24.0 pF/ft (78.7 pF/m)	77 Ohm	70%	70 ns/100m

Voltage

UL Voltage Rating

150 V RMS

Mechanical Characteristics

Temperature

UL Temperature	Operating
200°C	-55°C To +200°C

Bend Radius

Stationary Min.	Installation Min.
1.29 in (32.8 mm)	1.29 in (32.8 mm)

Max. Pull Tension:	51 lbs (23 kg)
Bulk Cable Weight:	15 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor, Indoor
Flammability / Reaction to Fire:	NFPA 262 (UL 910), IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca; CPR UKCA Class: Eca
NEC / UL Compliance:	Article 725, CL2P
Military Compliance:	Commercial, non-QPL product (M17/176-00002, MIL-STD-1553 Data Bus Cable)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	PF_81553_1# Elements@Conductor1:-In Stibo it was Blank and now changed to 2. 2)Size@Conductor1 :-In Stibo it was 24 now changed to 24AWG. 3)Color@Color Chart1 01 :- In stibo it was Blank now Changed to White & Blue. 4)Cable Diameter (Nominal)- In Stibo it was Blank Now Changed to 0.129 in. 5)Coverage@OuterShield1 2 - in stibo it was 93% Now changed to 90%.
--------	--

History

Update and Revision:	Revision Number: 0.473 Revision Date: 04-29-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
81553 006500	Blue	Reel	500 ft	612825195559	F Z
81553 0061000	Blue	Reel	1,000 ft	612825195542	F Z

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.