

Part Number: 83284



50 Ohm Coax, RG316, 26 AWG Stranded SCCCS, SPC Braid, FEP Jacket, commercial non-QPL product.

Product Description

RG-316/U, 26 AWG stranded (7x34) .020" silver-coated copper-covered steel conductor, insulation, silver-plated copper braid shield (95% coverage), FEP jacket, commercial non-QPL product.

Technical Specifications

Product Overview

Environmental Space:	Indoor/Outdoor
----------------------	----------------

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
26	Stranded	SPCCS - Silver Plated Copper Covered Steel	0.02 in	1

Conductor Count:	1
------------------	---

Insulation

Material	Material Trade Name	Nominal Diameter
TFE - Tetrafluoroethylene	Teflon®	0.060 in

Outer Shield Material

Type	Material	Coverage [%]
Braid	SPC - Silver Plated Copper	95 %

Outer Jacket Material

Material	Nominal Diameter
FEP - Fluorinated Ethylene Propylene	0.098 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Outer Conductor DCR
84.1 Ohm/1000ft	8.4 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Shield
29 pF/ft

Inductance

Nominal Inductance
0.067 µH/ft

Impedance

Nominal Characteristic Impedance
50 Ohm

Return Loss (RL)

Frequency [MHz]	Min. Structural Return Loss (SRL)
-----------------	-----------------------------------

1 MHz - 3 GHz	30 dB
---------------	-------

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	1.2 dB/100ft
10 MHz	2.7 dB/100ft
50 MHz	5.6 dB/100ft
100 MHz	8.3 dB/100ft
200 MHz	12 dB/100ft
400 MHz	17.5 dB/100ft
700 MHz	23.7 dB/100ft
900 MHz	27.3 dB/100ft
1000 MHz	29 dB/100ft
1500 MHz	36.5 dB/100ft
2000 MHz	42.5 dB/100ft
2400 MHz	47.2 dB/100ft
3000 MHz	53.6 dB/100ft

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.46 ns/ft	69.5 %

Voltage

Description	Voltage Rating [V]
900V RMS	900 V RMS

Electrical Characteristics Notes:	VSWR/SRL per M17/113-RG316
-----------------------------------	----------------------------

Temperature Range

Non-UL Temp Rating:	200°C
Operating Temp Range:	-70°C To +200°C

Mechanical Characteristics

Bulk Cable Weight:	10 lbs/1000ft
Max Recommended Pulling Tension:	21 lbs
Min Bend Radius/Minor Axis:	1 in

Standards

RG Type:	316/U Type
Military Specification:	Commercial, non-QPL product (M17/113-RG316)
QPL (Qualified Parts List):	No

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Aerial:	Yes - When supported by messenger wire
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	No

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	UPC	Length	Footnote
83284 009100	White	612825203797	100 ft	E
83284 0091000	White	612825203803	1,000 ft	E
83284 009500	White	612825206118	500 ft	E

Footnote:	E - MAY CONTAIN MORE THAN 1 PIECE. MINIMUM LENGTH OF ANY ONE PIECE IS 25'.
-----------	--

History

Update and Revision:	Revision Number: 0.283 Revision Date: 08-22-2019
----------------------	--

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.