



REPRESENTATIVE IMAGE

Product: [83321E](#)

Electronic, 2 C #18 Str SPC, TFE Ins, OA SPC Brd, TFE Jkt, MIL-W-16878/4 (Type E)

[Request Sample](#)

Product Description

High Temperature Electronic, 2 Conductor 18AWG (19x30) Silver Plated Copper, TFE Insulation, Overall Silver Plated Copper Braid(85%) Shield, TFE Outer Jacket, MIL-W-16878/4 (Type E)

Technical Specifications

Product Overview

Suitable Applications:	MIL-W-16878/4 (Type E) Spec; Extreme High/Low Temperature Environments; up to 600V analog signals & voltage control
------------------------	---

Construction Details

Conductor

Element	Number of Element	Size	Stranding	Material
Conductor(s)	2	18 AWG	19x30	SC - Silvered Copper

Insulation

Element	Material	Nom. Thickness	Color Code
Conductor(s)	PTFE - Polytetrafluoroethylene	0.0105 in (0.267 mm)	White, Black

Outer Shield

Shield Type	Material	Coverage
Braid	Silvered Copper (SC)	85%

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PTFE - Polytetrafluoroethylene	0.011 in (0.28 mm)	0.179 in (4.55 mm)

Cable Diameter (Nominal):	0.179 in (4.55 mm)
---------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
Conductor(s)	5.52 Ohm/1000ft (18.1 Ohm/km)	31 pF/ft (100 pF/m)	52.8 pF/ft (173 pF/m)	8.1 Amps per conductor @ 25°C

Voltage

Voltage Rating
600 V

Mechanical Characteristics

Temperature

Operating
-65°C to +200°C

Bend Radius

Stationary Min.	Installation Min.

1.8 in (46 mm)	1.8 in (46 mm)
----------------	----------------

Max. Pull Tension:	79.2 lbs (35.9 kg)
--------------------	--------------------

Bulk Cable Weight:	27 lbs/1000ft (40 kg/km)
--------------------	--------------------------

Standards and Compliance

Environmental Suitability:	Indoor
----------------------------	--------

Sustainability:	CA Prop 65
-----------------	------------

Flammability / Fire Resistance:	IEC 60332-1-2
---------------------------------	---------------

NEMA Compliance:	NEMA HP3
------------------	----------

Military Compliance:	MIL-W-16878/4 (Type E except stranding), (insulated conductors)
----------------------	---

CPR Euroclass:	Eca
----------------	-----

European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
--------------------------------	---

APAC Compliance:	China RoHS II (GB/T 26572-2011)
------------------	---------------------------------

Product Notes

Notes:	Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc.
--------	---

History

Update and Revision:	Revision Number: 0.366 Revision Date: 10-13-2021
----------------------	--

Variants

Item #	Color	Putup Type	Length	UPC
83321E 009100	White	Reel	100 ft	612825204053
83321E 009500	White	Reel	500 ft	612825204077
83321E 0091000	White	Reel	1,000 ft	612825204060

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.