



**Part Number: 8215**

Analog Video, RG6 #21 Solid BCCS, Double 95% BC Braids, PE Jacket

## Product Description

21 AWG solid .028" bare copper-covered steel conductor, polyethylene insulation, double bare copper braid shields (95% coverage), polyethylene jacket.

## Technical Specifications

### Product Overview

Environmental Space:	Outdoor - Direct Burial
----------------------	-------------------------

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
21	Solid	BCCS - Bare Copper Covered Steel	0.028 in	1

Conductor Count:	1
Conductor Size:	21 AWG

#### Insulation

Material	Nominal Diameter
PE - Polyethylene	0.185 in

#### Outer Shield Material

Type	Layer	Material	Coverage [%]
Braid	1	BC - Bare Copper	95 %
Braid	2	BC - Bare Copper	95 %

#### Outer Jacket Material

Material	Nominal Diameter
PE - Polyethylene	0.332 in

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR	Conductor Resistance	Nominal Outer Shield DCR	Outer Conductor DCR
32 Ohm/1000ft	32 Ohm/1000ft		1.1 Ohm/1000ft	1.1 Ohm/1000ft

#### Capacitance

Nom. Capacitance Conductor to Shield
20.5 pF/ft

Shielding:	Braid(s)
------------	----------

#### Inductance

Nominal Inductance
0.115 µH/ft

#### Impedance

Nominal Characteristic Impedance
75 Ohm

#### Return Loss (RL)

Frequency [MHz]	Minimum Return (RL)
5-450 MHz	23 dB

#### High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.4 dB/100ft
10 MHz	0.8 dB/100ft
50 MHz	1.9 dB/100ft
100 MHz	2.7 dB/100ft
200 MHz	4.1 dB/100ft
400 MHz	5.9 dB/100ft
700 MHz	8.1 dB/100ft
900 MHz	9.4 dB/100ft
1000 MHz	9.8 dB/100ft

#### Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.54 ns/ft	66 %

#### High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)
400 MHz	7.2 dB/100ft
10 MHz	
50 MHz	
100 MHz	
200 MHz	
400 MHz	
700 MHz	
900 MHz	
1000 MHz	

#### Voltage

Non-UL Voltage Rating
2700 V RMS

#### Temperature Range

Non-UL Temp Rating:	80°C
Operating Temp Range:	-55°C To +80°C

#### Mechanical Characteristics

Bulk Cable Weight:	69 lbs/1000ft
Max Recommended Pulling Tension:	180 lbs
Min Bend Radius/Minor Axis:	3.5 in

#### Standards

RG Type:	6A/U Type
Series Type:	Series 6
RG / Series Type:	Series 6

#### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	No
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Burial:	Yes
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes

## Part Number

### Variants

Item #	Color	Footnote
8215 0101000	Black	C

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.