



**Product:** [8216](#)

50 Ohm Wireless Transmission Coax, RG-174, 26 AWG Str BCCS, 90% TC Braid, PVC Jkt

### Product Description

50 Ohm Wireless Transmission Coax, RG-174, 26 AWG (7x34) Bare Copper Covered Steel Conductor , PE Insulation, 90% Tinned Copper Braid Shield, PVC Jacket

### Technical Specifications

#### Product Overview

Suitable Applications:	Point-to-point and point-to-multipoint wireless antenna communication; Wireless microphones, Two-Way Radios, Amateur (Ham) Radio, Low Power FM, GPS, RFID (Radio Frequency Identification)
------------------------	--

#### Construction Details

RG Type:	174
----------	-----

#### Conductor

AWG	Stranding	Nom. Diameter	Material
26	7x34	0.019 in	BCCS - Bare Copper Covered Steel

#### Insulation

Material	Nom. Diameter
PE - Polyethylene	0.060 in

#### Outer Shield Material

Outer Shield Type	Material	Coverage
Braid	Tinned Copper (TC)	90%

#### Outer Jacket Material

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.110 in

#### Electrical Characteristics

##### Attenuation

Frequency	Nom. Attenuation [dB/100ft]
1 MHz	1.9 dB/100ft
10 MHz	3.3 dB/100ft
50 MHz	5.8 dB/100ft
100 MHz	8.4 dB/100ft
200 MHz	12.5 dB/100ft
400 MHz	19.0 dB/100ft
700 MHz	27.0 dB/100ft
900 MHz	31.0 dB/100ft
1000 MHz	34.0 dB/100ft

##### Power Rating

Frequency [MHz]	Max. Power Rating [W]
1 MHz	976 W
10 MHz	354 W

50 MHz	197 W
100 MHz	161 W
200 MHz	136 W
400 MHz	120 W
700 MHz	112 W
900 MHz	109 W
1,000 MHz	108 W

#### Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Impedence
97 Ohm/1000ft	10.7 Ohm/1000ft	30.8 pF/ft	50 Ohm

#### Voltage

UL Voltage Rating	Non-UL Voltage Rating
30 V (UL AWM 1354)	1100 V

## Mechanical Characteristics

#### Temperature

UL Rating	Operating
60°C (UL AWM 1354)	-30°C to +75°C

#### Bend Radius

Installation Min.
1.1 in

Bulk Cable Weight:	8 lbs/1000ft
Max. Pull Tension:	20 lbs

## Standards and Compliance

Environmental Suitability:	Outdoor - Aerial, Indoor
Sustainability:	CA Prop 65
AWM Compliance:	1354
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## History

Update and Revision:	Revision Number: 0.330 Revision Date: 08-25-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.