



**Product:** [8219](#) 

50 Ohm Wireless Transmission Coax, RG-58, 20 AWG Str TC, 95% TC Braid, PVC Jkt, CM

### Product Description

50 Ohm Wireless Transmission Coax, RG-58, 20 AWG (19x32) Tinned Copper Conductor , PE Insulation, 95% Tinned Copper Braid Shield, PVC Jacket, CM

### Technical Specifications

#### Product Overview

Suitable Applications:	Point-to-point and point-to-multipoint wireless antenna communication; Wireless microphones, Two-Way Radios, Amateur (Ham) Radio, Low Power FM, GPS, RFID (Radio Frequency Identification)
------------------------	--

#### Construction Details

RG Type:	58
----------	----

#### Conductor

AWG	Stranding	Nom. Diameter	Material
20	19x32	0.037 in	TC - Tinned Copper

#### Insulation

Material	Nom. Diameter
PE - Polyethylene (Foam)	0.116 in

#### Outer Shield Material

Outer Shield Type	Material	Coverage
Braid	Tinned Copper (TC)	95%

#### Outer Jacket Material

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.193 in

#### Electrical Characteristics

##### Attenuation

Frequency	Nom. Attenuation [dB/100ft]
1 MHz	0.4 dB/100ft
10 MHz	1.3 dB/100ft
50 MHz	3.1 dB/100ft
100 MHz	4.5 dB/100ft
200 MHz	6.6 dB/100ft
400 MHz	10.0 dB/100ft
700 MHz	14.2 dB/100ft
900 MHz	16.6 dB/100ft
1000 MHz	18.1 dB/100ft

##### Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Impedance	Nom. Velocity
8.8 Ohm/1000ft	4.1 Ohm/1000ft	26.0 pF/ft	54 Ohm	76%

##### Voltage

**UL Voltage Rating**

300 V (CM), 30 V (UL AWM 1354)

**Mechanical Characteristics****Temperature**

UL Rating	Operating
80°C	-30°C to +75°C

**Bend Radius**

Installation Min.
1.9 in

Bulk Cable Weight:	26 lbs/1000ft
Max. Pull Tension:	50 lbs

**Standards and Compliance**

Environmental Suitability:	Outdoor - Aerial, Indoor
Sustainability:	CA Prop 65
Flammability / Fire Resistance:	UL1685 UL Loading, UN ECE R118.02
NEC / UL Compliance:	CM
AWM Compliance:	1354
CEC / C(UL) Compliance:	CM
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	P-MSHA-SC-182/5

**History**

Update and Revision:	Revision Number: 0.351 Revision Date: 09-30-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.