

**Part Number: 8240**

Distributed Antenna Systems (DAS) 52 Ohm, RG58, 20 AWG, CMX



## Product Description

Distributed Antenna Systems (DAS) Cable, RG-58A/U type, 20 AWG solid .033" bare copper conductor, polyethylene insulation, tinned copper braid shield (95% coverage), PVC jacket.

## Technical Specifications

### Product Overview

Environmental Space:	Outdoor - Aerial
----------------------	------------------

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
20	Solid	BC - Bare Copper	0.033 in	1

Conductor Count:	1
AWG Size:	20

#### Insulation

Material	Nominal Diameter
PE - Polyethylene	0.116 in

#### Outer Shield Material

Type	Material	Coverage [%]
Braid	TC - Tinned Copper	95 %

#### Outer Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.193 in

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
10 Ohm/1000ft	4.1 Ohm/1000ft

#### Capacitance

Nom. Capacitance Conductor to Shield
28.5 pF/ft

#### Inductance

Nominal Inductance
0.08 $\mu$ H/ft

#### Impedance

Nominal Characteristic Impedance
52 Ohm

#### High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.3 dB/100ft

10 MHz	1.1 dB/100ft
50 MHz	2.5 dB/100ft
100 MHz	3.8 dB/100ft
200 MHz	5.6 dB/100ft
400 MHz	8.4 dB/100ft
700 MHz	11.7 dB/100ft
900 MHz	13.7 dB/100ft
1000 MHz	14.5 dB/100ft

#### Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.54 ns/ft	66 %

#### Power Rating

Frequency [MHz]	Max. Power Rating [W]
50 MHz	530 W
100 MHz	350 W
400 MHz	160 W
1,000 MHz	90 W

#### Voltage

Non-UL Voltage Rating	UL Voltage Rating
1400V RMS	300V RMS (CMX), 30V RMS (UL AWM Style 1354)
	30V RMS (UL AWM Style 1354)

Electrical Characteristics Notes: Actual Impedance specification is 51.5 +/- 1.5 ohms.

#### Temperature Range

UL Temp Rating:	80°C (UL AWM Style 1354)
Operating Temp Range:	-40°C To +75°C

#### Mechanical Characteristics

UV Resistance:	Yes
Bulk Cable Weight:	26 lbs/1000ft
Max Recommended Pulling Tension:	47 lbs
Min Bend Radius/Minor Axis:	2 in

#### Standards

NEC/(UL) Specification:	CMX
CEC/C(UL) Specification:	CMX
UL AWM Style:	UL Style 1354
CPR Euroclass:	Eca
RG Type:	RG-58A/U Type

#### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	No
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

#### Suitability

Suitability - Aerial:	Yes - Black only, when supported by messenger wire
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes - Black only

## Flammability, LS0H, Toxicity Testing

UL Flammability:	VW-1
------------------	------

## Part Number

Plenum (Y/N):	No
Plenum Number:	88240, 82240

## Variants

Item #	Color	Footnote
8240 010100	BLACK	
8240 0101000	BLACK	C
8240 010500	BLACK	C
8240 0105000	BLACK	C
8240 010U1000	BLACK	
8240 010U500	BLACK	

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS(Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be instock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.