


Part Number: 8241B

Analog Video, RG59, #23 Solid BC, 95% BC Braid, PVC Jacket, CM



Product Description

23 AWG solid .023" bare copper conductor, polyethylene insulation, bare copper braid shield (95% coverage), PVC jacket.

Technical Specifications

Product Overview

Environmental Space:	Indoor Rated (Not Riser or Plenum)
----------------------	------------------------------------

Physical Characteristics (Overall)

Conductor

AWG	Material	Nominal Diameter	No. of Coax
23	BC - Bare Copper	0.023 in	1

Total Number of Conductors:	1
-----------------------------	---

Insulation

Material	Nominal Diameter
PE - Polyethylene	0.146 in

Outer Shield Material

Type	Material	Coverage [%]
Braid	BC - Bare Copper	95 %

Outer Jacket Material

Material	Nominal Diameter
PVC - Polyvinyl Chloride	0.242 in

Electrical Characteristics

Capacitance

Nom. Capacitance Conductor to Shield
20.5 pF/ft

Shielding:	Braid
------------	-------

Construction and Dimensions

Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR	Conductor Resistance	Nominal Outer Shield DCR	Outer Conductor DCR
20.4 Ohm/1000ft	20.4 Ohm/1000ft		2.9 Ohm/1000ft	2.9 Ohm/1000ft

Impedance

Nominal Characteristic Impedance
75 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
-----------------	---------------------

1 MHz	0.4 dB/100ft
10 MHz	1.1 dB/100ft
50 MHz	2.4 dB/100ft
100 MHz	3.4 dB/100ft
200 MHz	4.9 dB/100ft
400 MHz	7 dB/100ft
700 MHz	9.7 dB/100ft
900 MHz	11.1 dB/100ft
1000 MHz	12 dB/100ft

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.54 ns/ft	66 %

Inductance

Nominal Inductance
0.131 µH/ft

Power Rating

Frequency [MHz]	Max. Power Rating [W]
50 MHz	470 W
100 MHz	310 W
300 MHz	160 W
500 MHz	115 W
1,000 MHz	76 W

Voltage

Non-UL Voltage Rating	UL Voltage Rating	Voltage Rating [V]
1700 V RMS	300 V RMS	30 V RMS

Applicable Standards & Environmental Programs

CEC/C(UL) Specification:	CM
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	No
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Standards

NEC/(UL) Specification:	CM
RG Type:	RG-59/U Type
UL AWM Style:	UL Style 1354 (30 V 80°C)

Flame Test

UL Flammability:	UL1685 UL Loading
------------------	-------------------

Safety

UL Voltage Rating:	300V RMS
--------------------	----------

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Suitability - Outdoor:	Yes
------------------------	-----

Mechanical Characteristics

Operating Temp Range:	-20°C To +80°C
Bulk Cable Weight:	34(lbs/1000ft)
Max Recommended Pulling Tension:	62(lbs)
Min Bend Radius/Minor Axis:	2.5(in)

Temperature Range

UL Temp Rating:	80°C
-----------------	------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

© 2017 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS(Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be instock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.