

Part Number: 8262

50 Ohm Coax, RG58, 20 AWG Stranded TC, TC Braid, Non-contaminating PVC Jacket



Product Description

50 Ohm, RG-58C/U, 20 AWG stranded (19x33) .035" tinned copper conductor, polyethylene insulation, tinned copper braid shield (95% coverage), non-contaminating PVC jacket.

Technical Specifications

Product Overview

Environmental Space:	Indoor
----------------------	--------

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
20	19x33	TC - Tinned Copper	0.035 in	1

Total Number of Conductors:	1
-----------------------------	---

Insulation

Material	Nominal Diameter
PE - Polyethylene	0.115 in

Outer Shield Material

Type	Material	Coverage [%]
Braid	TC - Tinned Copper	95 %

Outer Jacket Material

Material	Nominal Diameter
PVCNC - Polyvinyl Chloride Non-Contaminating	0.195 in

Electrical Characteristics

Capacitance

Nom. Capacitance Conductor to Shield
30.8 pF/ft

Shielding:	Braid
------------	-------

Construction and Dimensions

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR	Outer Conductor DCR
10.8 Ohm/1000ft	4.1 Ohm/1000ft	4.1 Ohm/1000ft

Impedance

Nominal Characteristic Impedance
50 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.4 dB/100ft
10 MHz	1.4 dB/100ft
50 MHz	3.3 dB/100ft
100 MHz	4.9 dB/100ft
200 MHz	7.3 dB/100ft
400 MHz	11.5 dB/100ft
700 MHz	17 dB/100ft
900 MHz	20 dB/100ft
1000 MHz	21.5 dB/100ft

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.54 ns/ft	66 %

Inductance

Nominal Inductance
0.077 μ H/ft

Voltage

Non-UL Voltage Rating
1400V RMS

Applicable Standards & Environmental Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-10-01
CPR Euroclass:	Eca
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Standards

Military Specification:	MIL-C-17, M17/155-00001
RG Type:	RG-58C/U Type

Suitability

Suitability - Indoor:	Y
-----------------------	---

Mechanical Characteristics

Operating Temp Range:	-40°C To +85°C
Bulk Cable Weight:	24(lbs/1000ft)
Max Recommended Pulling Tension:	42(lbs)
Min Bend Radius/Minor Axis:	2(in)

Temperature Range

UL Temp Rating:	85°C
-----------------	------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

History

Variants

Item #	Color
8262 0101000	BLACK
8262 010500	BLACK
8262 010U1000	BLACK
8262 010U500	BLACK

© 2017 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS(Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be instock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.