

## Part Number: 8262



50 Ohm, RG58, 20 AWG Stranded TC, TC Braid, Non-contaminating PVC Jacket, Commercial Non-QPL Product

### Product Description

50 Ohm, RG-58C/U, 20 AWG stranded (19x33) .035" tinned copper conductor, polyethylene insulation, tinned copper braid shield (95% coverage), non-contaminating PVC jacket, commercial non-QPL product

### Technical Specifications

#### Product Overview

Environmental Space:	Outdoor - Aerial
----------------------	------------------

#### Physical Characteristics (Overall)

##### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
20	Stranded	TC - Tinned Copper	0.035 in	1

Conductor Count:	1
AWG Size:	20

##### Insulation

Material	Nominal Diameter
PE - Polyethylene	0.115 in

##### Outer Shield Material

Type	Material	Coverage [%]
Braid	TC - Tinned Copper	95 %

##### Outer Jacket Material

Material	Nominal Diameter
PVCNC - Polyvinyl Chloride Non-Contaminating	0.195 in

#### Electrical Characteristics

##### Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR	Outer Conductor DCR
10.8 Ohm/1000ft	4.1 Ohm/1000ft	4.1 Ohm/1000ft

##### Capacitance

Nom. Capacitance Conductor to Shield
30.8 pF/ft

##### Inductance

Nominal Inductance
0.077 µH/ft

##### Impedance

Nominal Characteristic Impedance
50 Ohm

##### High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.4 dB/100ft

10 MHz	1.4 dB/100ft
50 MHz	3.3 dB/100ft
100 MHz	4.9 dB/100ft
200 MHz	7.3 dB/100ft
400 MHz	11.5 dB/100ft
700 MHz	17 dB/100ft
900 MHz	20 dB/100ft
1000 MHz	21.5 dB/100ft

#### Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.54 ns/ft	66 %

#### Voltage

Non-UL Voltage Rating
1400V RMS

#### Temperature Range

UL Temp Rating:	85°C
Operating Temp Range:	-40°C To +80°C

#### Mechanical Characteristics

UV Resistance:	Yes - Black only
Bulk Cable Weight:	24 lbs/1000ft
Max Recommended Pulling Tension:	42 lbs
Min Bend Radius/Minor Axis:	2 in

#### Standards

CPR Euroclass:	Eca
RG Type:	58C/U Type
Military Specification:	Commerical, non-QPL product (M17/155-00001)
QPL (Qualified Parts List):	No

#### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-10-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

#### Suitability

Suitability - Aerial:	Yes - Black only, when supported by messenger wire
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes - Black only

#### Part Number

Plenum (Y/N):	No
---------------	----

#### Variants

Item #	Color	Footnote
8262 0101000	BLACK	C
8262 010500	BLACK	C
8262 010U1000	BLACK	

8262 010U500	BLACK	
--------------	-------	--

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

## Product Notes

Notes:	Non-SWR swept version of RG-58.
--------	---------------------------------

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS(Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be instock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.