



Product: [8412P](#)

Plenum Microphone Cable, 2 Conductor 20 AWG, CMP

Product Description
20 AWG, 2 stranded (7x28) high-conductivity TC conductors, FEP Teflon® insulation, TC braid shield (85%), FEP Teflon® jacket.

Technical Specifications

Product Overview

Suitable Applications:	Audio, Analog Audio, Microphone
------------------------	---------------------------------

Construction Details

Conductor

Size	Stranding	Material
20	7x28	TC - Tinned Copper

Insulation

Material	Nom. Insulation Diameter	Color Code
FEP - Fluorinated Ethylene Propylene	.074 in (1.9 mm)	Dark Blue, Clear

Outer Shield

Shield Type	Material	Coverage
Braid	Bare Copper (BC)	90%

Outer Jacket

Material	Nom. Diameter
FEP - Fluorinated Ethylene Propylene	0.198 in (5.03 mm)

Electrical Characteristics

Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Velocity of Prop.
9.5 Ohm/1000ft (31 Ohm/km)	18.4 pF/ft (60.4 pF/m)	33.1 pF/ft (109 pF/m)	70%

Voltage

UL Voltage Rating
300 V RMS

Mechanical Characteristics

Temperature

UL Temperature	Operating
60°C	-70°C to +200°C

Max. Pull Tension:	68 lbs (31 kg)
Bulk Cable Weight:	35 lbs/1000ft (52 kg/km)

Standards and Compliance

Environmental Suitability:	Outdoor - Aerial, Indoor, Aerial - Black only, When supported by messenger wire
----------------------------	---

Flammability / Reaction to Fire:	NFPA 262, FT6
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
Non-Plenum Number:	8412

History

Update and Revision:	Revision Number: 0.216 Revision Date: 02-15-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
8412P 010500	Black	Reel	500 ft	612825206415
8412P 0101000	Black	Reel	1,000 ft	612825397182
8412P 009500	White	Reel	500 ft	612825397175
8412P 0091000	White	Reel	1,000 ft	612825397168

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.