



Product: [8267](#)

Mil-Spec Coax, 50 Ohm, RG-213, 13 AWG Str BC, 95% BC Braid, PVC Jkt, CMX, Commercial Non-QPL

Product Description

Mil-Spec Coax, 50 Ohm, RG-213, 13 AWG (7x21) Bare Copper Conductor, PE Insulation, 95% Bare Copper Braid Shield, PVC Jacket (Non-Contaminating), CMX, Commercial, non-QPL

Technical Specifications

Product Overview

Suitable Applications:	Point-to-point and point-to-multipoint wireless antenna communication; Wireless microphones, Two-Way Radios, Amateur (Ham) Radio, Low Power FM, GPS, RFID (Radio Frequency Identification)
------------------------	--

Construction Details

RG Type:	213
----------	-----

Conductor

Size	Stranding	Nom. Diameter	Material
13 AWG	7x21	0.089 in	BC - Bare Copper

Insulation

Material	Nom. Insulation Diameter	Color Code
PE - Polyethylene	0.285 in (7.24 mm)	White

Outer Shield

Outer Shield Type	Material	Coverage
Braid	Bare Copper (BC)	95%

Outer Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride (Non-Contaminating)	0.405 in (10.3 mm)

Overall Cable Diameter (Nominal):	0.405 in (10.3 mm)
-----------------------------------	--------------------

Electrical Characteristics

Attenuation

Frequency	Nom. Attenuation
1 MHz	0.17 dB/100ft
10 MHz	0.55 dB/100ft
50 MHz	1.3 dB/100ft
100 MHz	1.9 dB/100ft
200 MHz	2.7 dB/100ft
400 MHz	4.1 dB/100ft
700 MHz	6.5 dB/100ft
900 MHz	7.6 dB/100ft
1000 MHz	8.0 dB/100ft
4000 MHz	21.5 dB/100ft

Power Rating

Frequency	Max. Power Rating
1 MHz	9,295 W
10 MHz	2,761 W
50 MHz	1,122 W
100 MHz	748 W
200 MHz	494 W
400 MHz	326 W
700 MHz	235 W
900 MHz	205 W
1,000 MHz	194 W
4,000 MHz	110 W

Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Characteristic Impedance	Nom. Velocity of Prop.
1.7 Ohm/1000ft	1.2 Ohm/1000ft (3.9 Ohm/km)	30.8 pF/ft (101 pF/m)	50 Ohm	66%

Voltage

UL Voltage Rating	Voltage Rating
300 V (CMX), 30 V (UL AWM 1354)	3700 V (Mil-Spec)

Mechanical Characteristics

Temperature

UL Temperature	Operating
60°C (UL AWM 1354)	-40°C to +80°C

Bend Radius

Installation Min.
4 in (100 mm)

Max. Pull Tension:	184 lbs (83.5 kg)
Bulk Cable Weight:	104 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor, Aerial - Black only, When supported by messenger wire
Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	VW-1
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	CMX
AWM Compliance:	AWM 1354
CEC / C(UL) Compliance:	CMX
Military Compliance:	Commercial, non-QPL product (M17/163-00001)
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.519 Revision Date: 04-29-2024
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
8267 010500	Black	Reel	500 ft	612825197539	C
8267 0101000	Black	Reel	1,000 ft	612825428411	C

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.