



**Product:** [84142](#)

Mil-Spec Coax, 50 Ohm, RG-142, 19 AWG Solid SCCS, Double 95% SC Braid, FEP Jkt, CMP, Commercial Non-QPL

**Product Description**

Mil-Spec Coax, 50 Ohm, RG-142, 19 AWG Solid Silvered Copper Covered Steel Conductor, PTFE Insulation, Double 95% Silvered Copper Braid Shield, FEP Jacket, CMP, Commercial, non-QPL

**Technical Specifications**

**Product Overview**

Suitable Applications:	Aerospace wireless communication
------------------------	----------------------------------

**Construction Details**

RG Type:	142
----------	-----

**Conductor**

AWG	Stranding	Nom. Diameter	Material
19	Solid	0.037 in	SCCS - Silvered Copper Covered Steel

**Insulation**

Material	Nom. Diameter
PTFE - Polytetrafluoroethylene	0.116 in

**Outer Shield Material**

Layer	Outer Shield Type	Material	Coverage
1	Braid	Silvered Copper (SC)	95%
2	Braid	Silvered Copper (SC)	95%

**Outer Jacket Material**

Material	Nom. Diameter
FEP - Fluorinated Ethylene Propylene	0.195 in

**Electrical Characteristics**

**VSWR**

Frequency [MHz]	Max. VSWR
1 MHz - 12.4 GHz	per M17/60-RG142

**Attenuation**

Frequency	Nom. Attenuation [dB/100ft]
1 MHz	0.3 dB/100ft
10 MHz	1.1 dB/100ft
50 MHz	2.7 dB/100ft
100 MHz	3.9 dB/100ft
200 MHz	5.6 dB/100ft
400 MHz	6.9 dB/100ft
700 MHz	11.0 dB/100ft
900 MHz	12.5 dB/100ft
1000 MHz	13.5 dB/100ft

2000 MHz	19.3 dB/100ft
3000 MHz	24.3 dB/100ft
5000 MHz	32.6 dB/100ft
8000 MHz	43.2 dB/100ft

#### Power Rating

Frequency [MHz]	Max. Power Rating [W]
50 MHz	3,500 W
100 MHz	2,400 W
400 MHz	1,100 W
1,000 MHz	650 W
3,000 MHz	330 W
8,000 MHz	180 W

#### Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Impedence	Nom. Velocity
19.0 Ohm/1000ft	2.3 Ohm/1000ft	29 pF/ft	50 Ohm	70%

#### Voltage

UL Voltage Rating	Non-UL Voltage Rating
300 V (CMP)	1400 V (Mil-Spec)

## Mechanical Characteristics

#### Temperature

UL Rating	Operating
200°C	-70°C to +200°C

#### Bend Radius

Installation Min.
2 in

Bulk Cable Weight:	42 lbs/1000ft
Max. Pull Tension:	104 lbs

## Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor, Outdoor, Sunlight Resistance
Sustainability:	CA Prop 65
Flammability / Fire Resistance:	NFPA 262
NEC / UL Compliance:	CMP
CEC / C(UL) Compliance:	CMP
Military Compliance:	Commercial, non-QPL product (M17/60-RG142)
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## History

Update and Revision:	Revision Number: 0.333 Revision Date: 09-30-2020
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.