



Product: [8281F](#) 

75 Ohm Analog Video Coax, RG-59, 21 AWG Str BC, Double 95% TC Braid, PVC Jkt. Flexible

Product Description

75 Ohm Analog Video Coax, RG-59, 21 AWG (7x29) Bare Copper (Compacted) Conductor , PE Insulation, Double 95% Tinned Copper Braid Shield, PVC Jacket, Flexible

Technical Specifications

Product Overview

Suitable Applications:	Standard analog video
------------------------	-----------------------

Construction Details

RG Type:	59
----------	----

Conductor

AWG	Stranding	Nom. Diameter	Material
21	7x29	0.032 in	BC-C - Bare Copper (Compacted)

Insulation

Material	Nom. Diameter
PE - Polyethylene	0.193 in

Outer Shield Material

Layer	Outer Shield Type	Material	Coverage
1	Braid	Tinned Copper (TC)	95%
2	Braid	Tinned Copper (TC)	95%

Outer Jacket Material

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.304 in

Electrical Characteristics

Return Loss (RL)

Frequency [MHz]	Min. Return Loss [dB]
2 - 216 MHz	27 dB
217 - 830 MHz	23 dB

Attenuation

Frequency	Nom. Attenuation [dB/100ft]
1 MHz	0.3 dB/100ft
3.6 MHz	0.5 dB/100ft
10 MHz	0.9 dB/100ft
71.5 MHz	2.5 dB/100ft
135 MHz	3.6 dB/100ft
270 MHz	5.1 dB/100ft
360 MHz	6 dB/100ft
540 MHz	7.4 dB/100ft

720 MHz	8.7 dB/100ft
750 MHz	8.9 dB/100ft
1000 MHz	10.5 dB/100ft

Electricals

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Impedance	Nom. Velocity
11.6 Ohm/1000ft	1.7 Ohm/1000ft	20.5 pF/ft	75 Ohm	66%

Voltage

Non-UL Voltage Rating
2900 V

Mechanical Characteristics

Temperature

Operating
-30°C to +75°C

Bend Radius

Installation Min.
3.0 in

Bulk Cable Weight:	61 lbs/1000ft
Max. Pull Tension:	89 lbs

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
Sustainability:	CA Prop 65
European Directive Compliance:	EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Compacted copper combines the Impedance uniformity of solid conductors and the "nick-resistance" of stranded conductors.
--------	--

History

Update and Revision:	Revision Number: 0.295 Revision Date: 09-30-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.