

Product: [8434](#) 

Electronic, 1 Pr+2 C #25 Str TC+TCCS, PE Ins, IS/OS, PVC Jkt



REPRESENTATIVE IMAGE

 [Request Sample](#)

Product Description

Electronic, 1 Pair+2 Conductors 25AWG (7x33) Tinned Copper+Tinned Copper Covered Steel, PE Insulation, Individual & Overall Beldfoil® Shield, PVC Outer Jacket

Technical Specifications

Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; computer communication; panel wiring
------------------------	---

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors	No. of Pairs
25	7x33	TC+TCCS - Tinned Copper + Tinned Copper Covered Steel		1
25		TC+TCCS - Tinned Copper + Tinned Copper Covered Steel	2	

Conductor Count:	4
Total Number of Pairs:	1

Insulation

Material	Nominal Wall Thickness
PE - Polyethylene	0.015 in
PE - Polyethylene	0.015 in

Color Chart

Color
Red & Black

Color Chart 2

Color
Green
White

Inner Shield Material

Element	Type	Material	Material Trade Name	Coverage [%]
Pair(s)	Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%
Conductor(s)	No Shield			

Table Notes:	Shorting Fold (Foil-out)
--------------	--------------------------

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	Tinned Copper & Tinned Copper Covered Steel	25	7x33

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.165 in	0.02 in

Electrical Characteristics

Conductor DCR

Element	Individual Pair Nominal Shield DCR	Nominal Conductor DCR
Pair(s)	18.9 Ohm/1000ft	45.5 Ohm/1000ft
Conductor(s)		45.5 Ohm/1000ft

Capacitance

Element	Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
Pair(s)	25 pF/ft	40 pF/ft

Inductance

Nominal Inductance
0.2 µH/ft

Current

Max. Recommended Current [A]
1.3 Amps per Conductor at 25°C

Voltage

Non-UL Voltage Rating
400 V RMS

Temperature Range

Non-UL Temp Rating:	80°C
UL Temp Rating:	80°C
Operating Temp Range:	-20°C To +80°C

Mechanical Characteristics

Bulk Cable Weight:	12 lbs/1000ft
Max. Pull Tension:	41 lbs
Min Bend Radius/Minor Axis:	1.75 in

Standards

CPR Euroclass:	Eca
----------------	-----

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
MII Order #39 (China RoHS):	Yes

Flammability, LS0H, Toxicity Testing

IEC Flammability:	IEC 60332-1-2
UL voltage rating:	400 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Putup Type	Length	UPC
8434 060100	Chrome	Reel	100 ft	612825207047
8434 060500	Chrome	Reel	500 ft	612825207061
8434 0601000	Chrome	Reel	1,000 ft	612825207054
8434 060U1000	Chrome	UnReel	1,000 ft	612825207030

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.344 Revision Date: 09-30-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.