



**Product:** [83269](#)

Mil-Spec Coax, 50 Ohm, RG-188, 26 AWG Str SCCS, 95% SC Braid, PTFE Tape Jkt, Commercial Non-QPL

**Product Description**

Mil-Spec Coax, 50 Ohm, RG-188, 26 AWG (7x34) Silvered Copper Covered Steel Conductor, PTFE Insulation, 95% Silvered Copper Braid Shield, PTFE Tape Jacket, Commercial, non-QPL

**Technical Specifications**

**Product Overview**

Suitable Applications:	Aerospace wireless communication
------------------------	----------------------------------

**Construction Details**

RG Type:	188
----------	-----

**Conductor**

AWG	Stranding	Nom. Diameter	Material
26	7x34	0.020 in	SCCS - Silvered Copper Covered Steel

**Insulation**

Material	Nom. Diameter
PTFE - Polytetrafluoroethylene	0.058 in

**Outer Shield Material**

Outer Shield Type	Material	Coverage
Braid	Silvered Copper (SC)	95%

**Outer Jacket Material**

Material	Nom. Diameter
PTFE - Polytetrafluoroethylene	0.100 in

**Electrical Characteristics**

**Attenuation**

Frequency	Nom. Attenuation [dB/100ft]
1 MHz	1.2 dB/100ft
10 MHz	2.7 dB/100ft
50 MHz	5.6 dB/100ft
100 MHz	8.3 dB/100ft
200 MHz	12.0 dB/100ft
400 MHz	17.5 dB/100ft
700 MHz	23.7 dB/100ft
900 MHz	27.3 dB/100ft
1000 MHz	29.0 dB/100ft

**Electricals**

Nom. Conductor DCR	Nom. Outer Shield DCR	Nom. Capacitance Cond-to-Shield	Nom. Impedance	Nom. Velocity
91.2 Ohm/1000ft	8.5 Ohm/1000ft	29 pF/ft	50 Ohm	70%

**Voltage**

<b>Non-UL Voltage Rating</b>
900 V (Mil-Spec)

## Mechanical Characteristics

### Temperature

<b>Operating</b>
-70°C to +200°C

### Bend Radius

<b>Installation Min.</b>
1 in

Bulk Cable Weight:	11 lbs/1000ft
Max. Pull Tension:	27 lbs

## Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
Sustainability:	CA Prop 65
Military Compliance:	Commercial, non-QPL product (similar to M17/113-RG188)
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## History

Update and Revision:	Revision Number: 0.331 Revision Date: 11-19-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.