



Product: [8443MN](#)

SpaceMaker™, 3 C #22 Str TC, PO Ins, PVC Jkt, AWM 2937



Request Sample

Product Description

SpaceMaker™, 3 Conductor 22AWG (19x34) Tinned Copper, PO Insulation, PVC Outer Jacket, AWM 2937

Technical Specifications

Construction Details

Conductor

| Element | No. of Elements | Size | Stranding | Material |
|--------------|-----------------|--------|-----------|--------------------|
| Conductor(s) | 3 | 22 AWG | 19x34 | TC - Tinned Copper |

Insulation

| Element | Material | Nom. Thickness | Nom. Insulation Diameter | Color Code |
|--------------|--------------------|--------------------|--------------------------|-------------------|
| Conductor(s) | PP - Polypropylene | 0.010 in (0.25 mm) | 0.050 in (1.3 mm) | Black, White, Red |

Outer Shield

| Material |
|-----------|
| No Shield |

Outer Jacket

| Material | Nom. Thickness | Nom. Diameter |
|--------------------------|--------------------|---------------|
| PVC - Polyvinyl Chloride | 0.016 in (0.41 mm) | 0.140 in |

Overall Cable Diameter (Nominal): 0.140 in

Electrical Characteristics

Electricals

| Nom. Conductor DCR | Nom. Capacitance Cond-to-Cond | Nom. Characteristic Impedence | Max. Current |
|--------------------|-------------------------------|-------------------------------|--------------------------------|
| 18.1 Ohm/1000ft | 16.6 pF/ft (54.5 pF/m) | 51 Ohm | 2.9 Amps per Conductor at 25°C |

Voltage

| UL Voltage Rating |
|-------------------|
| 300 V |

Mechanical Characteristics

Temperature

| UL Temperature | Operating |
|----------------|----------------|
| 80°C | -20°C To +80°C |

Bend Radius

| Stationary Min. | Installation Min. |
|--------------------|-------------------|
| 0.560 in (14.2 mm) | 0.560 in |

Max. Pull Tension: 28.5 lbs (12.9 kg)

Bulk Cable Weight: 12 lbs/1000ft

Standards and Compliance

| | |
|--------------------------------|---|
| Environmental Suitability: | Indoor |
| AWM Compliance: | AWM 2937 |
| European Directive Compliance: | EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE) |

History

| | |
|----------------------|--|
| Update and Revision: | Revision Number: 0.209 Revision Date: 05-05-2023 |
|----------------------|--|

Part Numbers

Variants

| Item # | Color | Putup Type | Length | UPC |
|----------------|-------------|------------|----------|--------------|
| 8443MN 006100 | Blue, Light | Reel | 100 ft | 612825386148 |
| 8443MN 0061000 | Blue, Light | Reel | 1,000 ft | 612825386155 |
| 8443MN 008100 | Gray | Reel | 100 ft | 612825386162 |
| 8443MN 0081000 | Gray | Reel | 1,000 ft | 612825384656 |
| 8443MN 004100 | Yellow | Reel | 100 ft | 612825386124 |
| 8443MN 0041000 | Yellow | Reel | 1,000 ft | 612825386131 |

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.