



Product: [8443](#)

Electronic, 3 C #22 Str TC, PVC Ins, PVC Jkt, CMG

[Request Sample](#)

Product Description

Electronic, 3 Conductor 22AWG (7x30) Tinned Copper, PVC Insulation, PVC Outer Jacket, CMG

Technical Specifications

Product Overview

| | |
|------------------------|---|
| Suitable Applications: | low voltage analog signals (4-20ma, 0-10v, ...); low voltage control (24v, ...); line level audio; voice communications; panel wiring |
|------------------------|---|

Construction Details

Conductor

| Element | Number of Element | Size | Stranding | Material |
|--------------|-------------------|--------|-----------|--------------------|
| Conductor(s) | 3 | 22 AWG | 7x30 | TC - Tinned Copper |

Insulation

| Element | Material | Nom. Thickness | Nom. Insulation Diameter | Color Code |
|--------------|--------------------------|--------------------|--------------------------|-------------------|
| Conductor(s) | PVC - Polyvinyl Chloride | 0.011 in (0.28 mm) | 0.050 in (1.3 mm) | Black, Red, Green |

Outer Jacket

| Material | Nom. Thickness | Nom. Diameter |
|--------------------------|--------------------|--------------------|
| PVC - Polyvinyl Chloride | 0.032 in (0.81 mm) | 0.172 in (4.37 mm) |

| | |
|-----------------------------------|--------------------|
| Overall Cable Diameter (Nominal): | 0.172 in (4.37 mm) |
|-----------------------------------|--------------------|

Electrical Characteristics

Electricals

| Element | Nom. Conductor DCR | Nom. Capacitance Cond-to-Cond | Max. Current |
|--------------|--------------------|-------------------------------|--------------------------------|
| Conductor(s) | 17.8 Ohm/1000ft | 34 pF/ft (110 pF/m) | 2.9 Amps per Conductor at 25°C |

Voltage

| UL Voltage Rating |
|-------------------------------|
| 300 V (CMG), 150 V (AWM 2576) |

Mechanical Characteristics

Temperature

| UL Temperature | Operating |
|----------------|----------------|
| 80°C | -20°C to +80°C |

Bend Radius

| Stationary Min. | Installation Min. |
|-----------------|-------------------|
| 1.7 in (43 mm) | 1.7 in (43 mm) |

| | |
|--------------------|----------------|
| Max. Pull Tension: | 27 lbs (12 kg) |
| Bulk Cable Weight: | 90 lbs/1000ft |

Standards and Compliance

| | |
|----------------------------|--------|
| Environmental Suitability: | Indoor |
|----------------------------|--------|

| | |
|----------------------------------|---|
| Flammability / Reaction to Fire: | UL 1685 FT4 Loading, FT4, IEC 60332-1-2 |
| CPR Compliance: | CPR Euroclass: Eca |
| NEC / UL Compliance: | Article 800, CMG |
| AWM Compliance: | AWM 2576 |
| CEC / C(UL) Compliance: | CMG |
| European Directive Compliance: | EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE) |
| APAC Compliance: | China RoHS II (GB/T 26572-2011) |

History

| | |
|----------------------|--|
| Update and Revision: | Revision Number: 0.470 Revision Date: 06-30-2022 |
|----------------------|--|

Part Numbers

Variants

| Item # | Color | Putup Type | Length | UPC |
|---------------|--------|------------|----------|--------------|
| 8443 060100 | Chrome | Reel | 100 ft | 612825207320 |
| 8443 060500 | Chrome | Reel | 500 ft | 612825207344 |
| 8443 060U500 | Chrome | UnReel | 500 ft | 612825207313 |
| 8443 0601000 | Chrome | Reel | 1,000 ft | 612825207337 |
| 8443 060U1000 | Chrome | UnReel | 1,000 ft | 612825207306 |
| 8443 0605000 | Chrome | Reel | 5,000 ft | 612825207351 |

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.