



Product: [83554](#)

Electronic, 4 C #22 Str TC, FEP Ins, OS+TC Brd, FEP Jkt, CMP

[Request Sample](#)

Product Description

High Temperature Electronic, 4 Conductor 22AWG (7x30) Tinned Copper, FEP Insulation, Overall Beldfoil®+Tinned Copper Braid(85%) Shield, FEP Outer Jacket, CMP

Technical Specifications

Product Overview

Suitable Applications:	extreme high/low temperature environments; chemical resistant; outdoor and burial applications; low voltage analog signals (4-20ma, 0-10v, ...); low voltage control (24v, ...); line level audio; voice communications; panel wiring
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	4	22 AWG	7x30	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	FEP - Fluorinated Ethylene Propylene	0.0065 in (0.17 mm)	0.042 in (1.1 mm)	Black, White, Red, Green

Outer Shield

Shield Type	Material	Coverage
Tape	Bi-Laminate (Alum+Poly)	100%
Braid	Tinned Copper (TC)	85%

Outer Jacket

Separator	Material	Nom. Thickness	Nom. Diameter
Polyester Tape	FEP - Fluorinated Ethylene Propylene	0.015 in (0.38 mm)	0.161 in (4.09 mm)

Overall Cable Diameter (Nominal):	0.161 in (4.09 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Max. Current
Conductor(s)	15.5 Ohm/1000ft	23 pF/ft (75 pF/m)	40 pF/ft (130 pF/m)	2.2 Amps per Conductor at 25°C

Voltage

UL Voltage Rating
300 V (CMP)

Mechanical Characteristics

Temperature

UL Temperature	Operating
150°C	-70°C to +200°C

Bend Radius

Stationary Min.	Installation Min.
1.61 in (40.9 mm)	1.61 in (40.9 mm)

Max. Pull Tension:	36 lbs (16 kg)
Bulk Cable Weight:	25 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Plenum, Indoor, Outdoor, Sunlight Resistance, Oil Resistance
Flammability / Reaction to Fire:	NFPA 262, UL 910 (Plenum), FT6
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMP
CEC / C(UL) Compliance:	CMP
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Gas Resistant
--------	---------------

History

Update and Revision:	Revision Number: 0.510 Revision Date: 11-27-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
83554 002100	Red	Reel	100 ft	612825204954	
83554 002500	Red	Reel	500 ft	612825204978	C
83554 0021000	Red	Reel	1,000 ft	612825204961	C

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.