



**Product:** [8458](#)

Electronic, 15 C #22 Str TC, PVC Ins, PVC Jkt, CMG

[Request Sample](#)

## Product Description

Electronic, 15 Conductor 22AWG (7x30) Tinned Copper, PVC Insulation, PVC Outer Jacket, CMG

## Technical Specifications

### Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage control (24v, ...); line level audio; voice communications; panel wiring
------------------------	---

### Construction Details

#### Conductor

Element	Number of Element	Size	Stranding	Material
Conductor(s)	15	22 AWG	7x30	TC - Tinned Copper

#### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.011 in (0.28 mm)	0.050 in (1.3 mm)	Black, White, Red, Green, Orange, Blue, White/Black Stripe, Red/Black Stripe, Green/Black Stripe, Orange/Black Stripe, Blue/Black Stripe, Black/White Stripe, Red/White Stripe, Green/White Stripe, Blue/White Stripe

#### Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.040 in (1.0 mm)	0.315 in (8.00 mm)

Overall Cable Diameter (Nominal):	0.315 in (8.00 mm)
-----------------------------------	--------------------

### Electrical Characteristics

#### Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
Conductor(s)	18 Ohm/1000ft	34 pF/ft (110 pF/m)	4.2 Amps per Conductor at 30°C

#### Voltage

UL Voltage Rating
150 V (CMG), 150 V (UL AWM 2576)

### Mechanical Characteristics

#### Temperature

UL Temperature	Operating
80°C	-20°C to +80°C

#### Bend Radius

Stationary Min.	Installation Min.
3.2 in (81 mm)	3.2 in (81 mm)

Max. Pull Tension:	137 lbs (62.1 kg)
Bulk Cable Weight:	64 lbs/1000ft

### Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	UL 1685 FT4 Loading, FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMG
AWM Compliance:	AWM 2576
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## History

Update and Revision:	Revision Number: 0.473 Revision Date: 06-30-2022
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC
8458 060100	Chrome	Reel	100 ft	612825208037
8458 060500	Chrome	Reel	500 ft	612825208051
8458 0601000	Chrome	Reel	1,000 ft	612825208044
8458 0605000	Chrome	Reel	5,000 ft	612825208068

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.