



**Product:** [8404](#)

Microphone Cable, Star Quad, 4 C #20 Str TC, Rayon & 85% TC Braid, PVC Jkt

## Product Description

Microphone Cable, Star Quad, 4 Conductor 20 AWG (19 x 32) Tinned Copper (High conductivity), PE Insulation, Rayon® Braid, 85% Tinned Copper Braid Shield, PVC jacket

## Technical Specifications

### Product Overview

Suitable Applications:	Low frequency microphone or musical instruments; Balanced analog audio; Low Noise for high-EMI environments
------------------------	---

### Construction Details

#### Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	4	20 AWG	19x32	TC - Tinned Copper (High Conductivity)

#### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PE - Polyethylene	0.016 in (0.41 mm)	0.069 in (1.8 mm)	Clear, Black, Red, Green

#### Outer Shield

Shield Type	Material	Coverage
Braid	Rayon®	85%
Braid	Tinned Copper (TC)	85%

#### Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.032 in (0.81 mm)	0.252 in (6.40 mm)

Overall Cable Diameter (Nominal):	0.252 in (6.40 mm)
-----------------------------------	--------------------

### Electrical Characteristics

#### Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Characteristic Impedance	Nom. Velocity of Prop.	Max. Current
Conductor(s)	10.2 Ohm/1000ft	23 pF/ft (75 pF/m)	45 Ohm	66%	3.1 Amps per conductor @ 25°C

#### Voltage

UL Voltage Rating
300 V

### Mechanical Characteristics

#### Temperature

UL Temperature	Operating
60°C	-20°C to +60°C

#### Bend Radius

Stationary Min.	Installation Min.

2.5 in (64 mm)	2.5 in (64 mm)
----------------	----------------

Max. Pull Tension:	100 lbs (45 kg)
--------------------	-----------------

Bulk Cable Weight:	46 lbs/1000ft
--------------------	---------------

## Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
----------------------------	--------------------------------------

Flammability / Reaction to Fire:	VW-1
----------------------------------	------

AWM Compliance:	AWM 2094
-----------------	----------

European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
--------------------------------	---

APAC Compliance:	China RoHS II (GB/T 26572-2011)
------------------	---------------------------------

## Product Notes

Notes:	Overall cabling separator material: Rayon braid. Quad connection scheme: The two blue wires (or wires directly opposite one another) are connected together to form one conductor, and similarly the two white wires (or remaining wires) are connected together to form the second conductor.
--------	--

## History

Update and Revision:	Revision Number: 0.496 Revision Date: 01-20-2023
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC	Footnote
8404 060100	Chrome	Reel	100 ft	612825206187	
8404 060500	Chrome	Reel	500 ft	612825206163	C
8404 0601000	Chrome	Reel	1,000 ft	612825206194	C
8404 060U1000	Chrome	UnReel	1,000 ft	612825206200	

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.