



REPRESENTATIVE IMAGE

Product: [8473](#)

Electronic, 2 C #14 Str TC, PVC Ins, PVC Jkt, CL3

[Request Sample](#)

Product Description

Electronic, 2 Conductor 14AWG (42x30) Tinned Copper, PVC Insulation, PVC Outer Jacket, CL3

Technical Specifications

Product Overview

Suitable Applications:	up to 600V analog signals ; up to 600V digital control ; line level audio; voice communications; panel wiring
------------------------	---

Construction Details

Conductor

Element	Number of Element	AWG	Stranding	Material
Pair(s)	1	14	42x30	TC - Tinned Copper

Insulation

Element	Material	Thickness	Color Code
Pair(s)	PVC - Polyvinyl Chloride	0.032 in	Black & White

Outer Jacket Material

Material	Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.040 in	0.356 in

Cable Diameter (Nominal):	0.356 in
---------------------------	----------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
Pair(s)	2.86 Ohm/1000ft	22 pF/ft	9.6 Amps per Conductor at 25°C (10°C Temperature Rise)

Voltage

UL Voltage Rating
300 V (CL3), 600 V (UL AWM 2587)

Mechanical Characteristics

Temperature

UL Rating	Operating
90°C (UL AWM 2587)	-20°C to +90°C

Bend Radius

Stationary Min.	Installation Min.
3.5 in	3.6 in

Max. Pull Tension:	94 lbs
Bulk Cable Weight:	58 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor
Sustainability:	CA Prop 65
Flammability / Fire Resistance:	UL1685 UL Loading, FT1, IEC 60332-1-2
NEC / UL Compliance:	Article 725, CL3
AWM Compliance:	2587, FAS90
CPR Euroclass:	Eca
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Nominal Breakdown Voltage - Jacket 20 KV RMS; Nominal Breakdown Voltage Between Conductors 25 KV RMS. See NEC guidelines for applicable CL3 voltage ratings.
--------	--

History

Update and Revision:	Revision Number: 0.340 Revision Date: 09-30-2020
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.