



Product: [8618MN](#)

SpaceMaker™, 3 C #16 Str TC, PO Ins, OS, PVC Jkt, AWM 2937

### Product Description

SpaceMaker™, 3 Conductor 16AWG (65x34) Tinned Copper, PO Insulation, Overall Beldfoil® Shield, PVC Outer Jacket, AWM 2937

### Technical Specifications

#### Construction Details

##### Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	3	16	65x34	TC - Tinned Copper

##### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PP - Polypropylene	0.010 in (0.25 mm)	0.074 in (1.9 mm)	Black, White, Red

##### Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	16 AWG (19x29) TC

##### Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.016 in (0.41 mm)	0.196 in

Overall Cable Diameter (Nominal): 0.194 in (4.93 mm)

#### Electrical Characteristics

##### Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
4.4 Ohm/1000ft	31 pF/ft (100 pF/m)	6.2 Amps per Conductor at 25°C

##### Voltage

UL Voltage Rating
300 V

#### Mechanical Characteristics

##### Temperature

UL Temperature	Operating
80°C	-20°C To 80°C

Max. Pull Tension: 130 lbs (59 kg)

Bulk Cable Weight: 40 lbs/1000ft

#### Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	FT2
NEC / UL Compliance:	Article 800

AWM Compliance:	AWM 2937
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## History

Update and Revision:	Revision Number: 0.49 Revision Date: 04-04-2025
----------------------	---

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC
8618MN 006100	Blue, Light	Reel	100 ft	612825431053
8618MN 0061000	Blue, Light	Reel	1,000 ft	612825431060
8618MN 008100	Gray	Reel	100 ft	612825431077
8618MN 0081000	Gray	Reel	1,000 ft	612825431084
8618MN 004100	Yellow	Reel	100 ft	612825431039
8618MN 0041000	Yellow	Reel	1,000 ft	612825431046

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.