



Product: [8622](#)

Electronic, 12 C #16 Str TC, PVC Ins, PVC Jkt

[Request Sample](#)

Product Description

Electronic, 12 Conductor 16AWG (19x29) Tinned Copper, PVC Insulation, PVC Outer Jacket

Technical Specifications

Product Overview

Suitable Applications:	Analog Signals & Control (up to 600V); Line Level Audio; Voice Communications; Panel Wiring
------------------------	---

Construction Details

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	12	16 AWG	19x29	TC - Tinned Copper

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.031 in (0.79 mm)	0.121 in (3.07 mm)	Black, White, Red, Green, Orange, Blue, White/Black Stripe, Red/Black Stripe, Green/Black Stripe, Orange/Black Stripe, Blue/Black Stripe, Black/White Stripe

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.060 in (1.5 mm)	0.627 in (15.9 mm)
Overall Cable Diameter (Nominal):		0.627 in (15.9 mm)

Electrical Characteristics

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
Conductor(s)	4.45 Ohm/1000ft	19.5 pF/ft (64.0 pF/m)	8.4 Amps per Conductor at 30°C

Voltage Rating
600 V

Mechanical Characteristics

Operating
-30°C to +75°C

Stationary Min.	Installation Min.
6.3 in (160 mm)	6.3 in (160 mm)

Max. Pull Tension:	480 lbs (220 kg)
Bulk Cable Weight:	235 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	UL 1581 (VW-1), IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.511 Revision Date: 01-20-2023
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
8622 060100	Chrome	Reel	100 ft	612825213550	
8622 060500	Chrome	Reel	500 ft	612825213581	C
8622 0601000	Chrome	Reel	1,000 ft	612825213567	C
8622 0602000	Chrome	Reel	2,000 ft	612825213574	C Z

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.