



Product: [8469](#)

Electronic, 9 C #18 Str TC, PVC Ins, PVC Jkt, CMG

Request Sample

Product Description

Electronic, 9 Conductor 18AWG (19x30) Tinned Copper, PVC Insulation, PVC Outer Jacket, CMG

Technical Specifications

Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage control (24v, ...); line level audio; voice communications; panel wiring
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	9	18 AWG	19x30	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.018 in (0.46 mm)	0.080 in (2.0 mm)	Black, White, Red, Green, Brown, Blue, Orange, Yellow, Purple

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.037 in (0.94 mm)	0.364 in (9.25 mm)

Overall Cable Diameter (Nominal):	0.364 in (9.25 mm)
-----------------------------------	--------------------

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
Conductor(s)	7.13 Ohm/1000ft	26 pF/ft (85 pF/m)	9.8 Amps per Conductor at 30°C

Voltage

UL Voltage Rating
300 V (CMG), 300 V (UL AWM 2598)

Mechanical Characteristics

Temperature

UL Temperature	Operating
60°C	-20°C to +60°C

Bend Radius

Stationary Min.	Installation Min.
3.6 in (91 mm)	3.6 in (91 mm)

Max. Pull Tension:	222 lbs (101 kg)
Bulk Cable Weight:	89 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	UL 1685 FT4 Loading, FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CMG
AWM Compliance:	AWM 2598
CEC / C(UL) Compliance:	CMG
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.504 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
8469 060100	Chrome	Reel	100 ft	612825208440	
8469 060250	Chrome	Reel	250 ft	612825208464	C
8469 060500	Chrome	Reel	500 ft	612825208471	C
8469 0601000	Chrome	Reel	1,000 ft	612825208457	C
8469 0605000	Chrome	Reel	5,000 ft	612825208488	

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.