



**Product:** [8489](#) 

Electronic, 4 C #18 Str TC, PVC Ins, PVC Jkt, CMG

 [Request Sample](#)

## Product Description

Electronic, 4 Conductor 18AWG (19x30) Tinned Copper, PVC Insulation, PVC Outer Jacket, CMG

## Technical Specifications

### Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage control (24v, ...); line level audio; voice communications; panel wiring
------------------------	---

### Construction Details

#### Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	4	18 AWG	19x30	TC - Tinned Copper

#### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC - Polyvinyl Chloride	0.018 in (0.46 mm)	0.081 in (2.1 mm)	Black, White, Red, Green

#### Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.032 in (0.81 mm)	0.264 in (6.71 mm)

Overall Cable Diameter (Nominal): 0.264 in (6.71 mm)

### Electrical Characteristics

#### Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Max. Current
Conductor(s)	7.06 Ohm/1000ft	26 pF/ft (85 pF/m)	11.2 Amps per Conductor at 30°C

#### Voltage

UL Voltage Rating
300 V (CMG), 300 V (UL AWM 2598)

### Mechanical Characteristics

#### Temperature

UL Temperature	Operating
60°C	-20°C to +60°C

#### Bend Radius

Stationary Min.	Installation Min.
2.6 in (66 mm)	2.6 in (66 mm)

Max. Pull Tension: 99 lbs (45 kg)

Bulk Cable Weight: 44 lbs/1000ft

### Standards and Compliance

Environmental Suitability:	Indoor
----------------------------	--------

Flammability / Reaction to Fire:	UL 1685 UL loading , FT4, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 725, Article 800, CMG, CL3
AWM Compliance:	AWM 2598
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Plenum Number:	88489, 82489

## History

Update and Revision:	Revision Number: 0.516 Revision Date: 09-07-2025
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC	Footnote
8489 060100	Chrome	Reel	100 ft	612825208754	
8489 060250	Chrome	Reel	250 ft	612825208778	
8489 060500	Chrome	Reel	500 ft	612825208785	C
8489 060U500	Chrome	UnReel	500 ft	612825208747	
8489 0601000	Chrome	Reel	1,000 ft	612825208761	C
8489 060U1000	Chrome	UnReel	1,000 ft	612825208730	
8489 0605000	Chrome	Reel	5,000 ft	612825208792	

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.