



Product: [85164](#)

Electronic, 4 Pr #20 Str TC, ETFE Ins, OS, ETFE Jkt

[Request Sample](#)

Product Description

High Temperature Electronic, 4 Pair 20AWG (7x28) Tinned Copper, ETFE Insulation, Overall Beldfoil® Shield, ETFE Outer Jacket

Technical Specifications

Product Overview

Suitable Applications:	extreme high/low temperature environments; chemical resistant; low voltage analog signals (4-20ma, 0-10v, ...); low voltage control (24v, ...); instrumentation
------------------------	---

Construction Details

Conductor

Element	Number of Element	Size	Stranding	Material
Pair(s)	4	20	7x28	TC - Tinned Copper

Insulation

Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
ETFE - Ethylene Tetrafluoroethylene	0.015 in (0.38 mm)	0.068 in (1.7 mm)	Black & Red, Black & White, Black & Green, Black & Blue

Outer Shield

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Nomex®)	100%	22 AWG (7x30) TC

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
ETFE - Ethylene Tetrafluoroethylene	0.025 in (0.64 mm)	0.344 in

Electrical Characteristics

Electricals

Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedence	Max. Current
10.92 Ohm/1000ft	23 pF/ft (75 pF/m)	40 pF/ft (130 pF/m)	73 Ohm	6.4 Amps per Conductor at 25°C

Voltage

Voltage Rating
300 V

Mechanical Characteristics

Temperature

UL Temperature	Operating
150°C	-60°C To +150°C

Bend Radius

Stationary Min.	Installation Min.
3.44 in (87.4 mm)	3.44 in

Max. Pull Tension:	109.8 lbs (49.80 kg)
Bulk Cable Weight:	66 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Tefzel and Kapton are DuPont trademarks.
--------	--

History

Update and Revision:	Revision Number: 0.378 Revision Date: 04-08-2022
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC
85164 368100	Clear, Transparent	Reel	100 ft	612825210627
85164 3681000	Clear, Transparent	Reel	1,000 ft	612825210634

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.