



Part Number: 8762

Audio/Control/Instrumentation, (1 pr) 20 AWG (7x28) TC, PE/PVC, Foil Shld, CM

[Request Sample](#)

Product Description

One 20 AWG pair stranded (7x28) TC conductors, polyethylene insulation, twisted pair, overall Beldfoil® shield (100% coverage), PVC jacket.

Technical Specifications

Physical Characteristics (Overall)

Conductor			
AWG	Stranding	Material	No. of Pairs
20	7x28	TC - Tinned Copper	1
Conductor Count:		2	
Total Number of Pairs:		1	
Conductor Size:		20 AWG	

Insulation	
Material	Nominal Wall Thickness
PE - Polyethylene	0.017 in

Color Chart	
Number	Color
1	Black & Clear

Outer Shield Material						
Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum/Polyester	Beldfoil®	100 %	TC - Tinned Copper	20	7x28 mm

Outer Jacket Material		
Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.204 in	0.028 in

Construction and Dimensions

Cabling	
Lay Direction	Twists
Left Hand	6 twist/ft

Electrical Characteristics

Conductor DCR
Nominal Conductor DCR
9.5 Ohm/1000ft

Capacitance	
Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
27 pF/ft	49 pF/ft

Inductance
Nominal Inductance
0.18 µH/ft

Impedance

Nominal Characteristic Impedance

56 Ohm

Current

Element	Max. Recommended Current [A]
10C temperature rise	3.9 Amps per conductor @ 25°C ambient

Voltage

UL Voltage Rating

300 V RMS

Temperature Range

UL Temp Rating:	60°C (UL AWM Style 2092)
Operating Temp Range:	-20°C To +60°C

Mechanical Characteristics

Bulk Cable Weight:	21 lbs/1000ft
Max Recommended Pulling Tension:	46 lbs
Min Bend Radius/Minor Axis:	2.25 in

Standards

NEC Articles:	800
NEC/(UL) Specification:	CM
CEC/C(UL) Specification:	CM
UL AWM Style:	UL Style 2092 (300 V 60°C)
CPR Euroclass:	Eca

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1685 UL Loading
CSA Flammability:	FT1
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Footnote
8762.00U152	Chrome	
8762.00U305	Chrome	
8762.01152	Chrome	
8762.01305	Chrome	
8762 060100	Chrome	

8762 0601000	Chrome	C
8762 06010000	Chrome	C Y
8762 0602000	Chrome	C
8762 060250	Chrome	
8762 060500	Chrome	C
8762 060U1000	Chrome	
8762 060U500	Chrome	

Footnote:	C - CRATE REEL PUT-UP.
Footnote:	Y - FINAL PUT-UP LENGTH MAY VAR -10% TO +20% FROM LENGTH SHOWN. MAY CONTAIN 2 PIECES. MINIMUM LENGTH OF ANY ONE PIECE IS 1500'.

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.