



Part Number: 8762

Electronic, 2 C #20 Str TC, PO Ins, OS, PVC Jkt, CM

[Request Sample](#)

Product Description

Electronic, 2 Conductor 20AWG (7x28) Tinned Copper, PO Insulation, Overall Beldfoil® Shield, PVC Outer Jacket, CM, Suitable for Audio, Control, and Instrumentation Applications

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
20	7x28	TC - Tinned Copper	1

Conductor Count:	2
Total Number of Pairs:	1

Insulation

Material	Nominal Wall Thickness
PE - Polyethylene	0.017 in

Color Chart

Number	Color
1	Black & Clear

Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum/Polyester	Beldfoil®	100 %	TC - Tinned Copper	20	7x28 mm

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.204 in	0.028 in

Construction and Dimensions

Cabling

Lay Direction	Twists
Left Hand	6 twist/ft

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
9.5 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
27 pF/ft	49 pF/ft

Inductance

Nominal Inductance

0.18 µH/ft

Impedance

Nominal Characteristic Impedance

56 Ohm

Current

Element	Max. Recommended Current [A]
10C temperature rise	3.9 Amps per conductor @ 25°C ambient

Voltage

UL Voltage Rating

300 V RMS

Temperature Range

UL Temp Rating:	60°C (UL AWM Style 2092)
Operating Temp Range:	-20°C To +60°C

Mechanical Characteristics

Bulk Cable Weight:	21 lbs/1000ft
Max Recommended Pulling Tension:	46 lbs
Min Bend Radius/Minor Axis:	2.25 in

Standards

NEC Articles:	800
NEC/(UL) Specification:	CM
CEC/C(UL) Specification:	CM
UL AWM Style:	UL Style 2092 (300 V 60°C)
CPR Euroclass:	Eca

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1685 UL Loading
CSA Flammability:	FT1
ISO/IEC Flammability:	IEC 60332-1-2
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	UPC	Length	Footnote
8762.00U152	Chrome		152 m	
8762.00U305	Chrome		305 m	
8762.01152	Chrome		152 m	

8762.01305	Chrome		305 m	
8762.01610	Chrome		610 m	
8762 060100	Chrome	612825215363	100 ft	
8762 0601000	Chrome	612825215370	1,000 ft	C
8762 06010000	Chrome	612825215387	10,000 ft	C Y
8762 0602000	Chrome	612825215394	2,000 ft	C
8762 060250	Chrome	612825215400	250 ft	
8762 060500	Chrome	612825215417	500 ft	C
8762 060U1000	Chrome	612825215349	1,000 ft	
8762 060U500	Chrome	612825215356	500 ft	
8762.K1305	Chrome		305 m	

Footnote:	C - CRATE REEL PUT-UP.
Footnote:	Y - FINAL PUT-UP LENGTH MAY VAR -10% TO +20% FROM LENGTH SHOWN. MAY CONTAIN 2 PIECES. MINIMUM LENGTH OF ANY ONE PIECE IS 1500'.

History

Update and Revision:	Revision Number: 0.300 Revision Date: 08-22-2019
----------------------	--

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.