



**Product:** [8663](#)

Shielding & Bonding, TC Braid #11.9AWG

[Request Sample](#)

**Product Description**

Shielding & Bonding, TC Braid 11.9AWG (168x34)

**Technical Specifications**

**Product Overview**

Suitable Applications:	for shielding and bonding cable
------------------------	---------------------------------

**Construction Details**

**Conductor**

Size	Stranding	Material
11.9	168x34	TC - Tinned Copper

**Electrical Characteristics**

**Electricals**

Nom. Conductor DCR	Max. Current
1.55 Ohm/1000ft (5.09 Ohm/km)	Single conductor in free air @ 30°C: 38.0 A

**Mechanical Characteristics**

Bulk Cable Weight:	24 lbs/1000ft (36 kg/km)
--------------------	--------------------------

**Standards and Compliance**

Sustainability:	CA Prop 65
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)

**Product Notes**

Notes:	AWG size is approximated.
--------	---------------------------

**History**

Update and Revision:	Revision Number: 0.347 Revision Date: 04-08-2022
----------------------	--

**Part Numbers**

**Variants**

Item #	Color	Putup Type	Length	UPC
8663 00050	None	Reel	50 ft	612825213949
8663 000250	None	Reel	250 ft	612825213932

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.