



Product: [8787](#)



Audio, Control and Instrumentation, 8 Conductor 24 AWG, Shielded Quads; 2 Conductor 22 AWG Unshielded

Product Description

8 Conductor 24 AWG stranded (7x32) TC, shielded quads, polyethylene insulation, 24 AWG stranded TC drain wire; 2 Conductor 22 AWG stranded (7x30) TC, Unshielded, PVC insulation, PVC jacket.

Technical Specifications

Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; computer communication; panel wiring
------------------------	-------------------------------------------------------------------------------------------------------------------------------------------------

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	8	24 AWG	7x32	TC - Tinned Copper
Conductor(s)	2	22 AWG	7x30	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PE - Polyethylene	0.012 in (0.30 mm)	0.048 in (1.2 mm)	Red Quad, White, Green Quad, Blue
Conductor(s)	PVC - Polyvinyl Chloride	0.015 in (0.38 mm)	0.060 in (1.5 mm)	Gray, White, Blue, Green, Red Beldfoil®, Brown, Red, Yellow, Orange, Green Beldfoil®, White, Blue, Unshielded

Inner Shield

Element	Shield Type	Material	Coverage	Drainwire Type
Over Quad	Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC
Over Quad	Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC

Table Notes:	Gray, White, Blue, Green; Brown, Red, Yellow, Orange; White, Blue
--------------	-------------------------------------------------------------------

Outer Shield

Material
No Shield

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.03 in (0.76 mm)	0.29 in

Overall Cable Diameter (Nominal):	0.29 in.
-----------------------------------	----------

Electrical Characteristics

Electricals

Nom. Conductor DCR	Nom. Inner Shield DCR	Max. Current
28.7 Ohm/1000ft	15.79 Ohm/1000ft (51.80 Ohm/km)	1.5 Amps per Conductor at 25°C (24 AWG)
15 Ohm/1000ft (49 Ohm/km)	15.79 Ohm/1000ft (51.80 Ohm/km)	3 Amps per Conductor at 25°C (22 AWG)

Voltage

Voltage Rating
350 V

Mechanical Characteristics

Temperature

Operating
-20°C To +80°C

Bend Radius

Stationary Min.	Installation Min.
2.9 in (74 mm)	2.9 in

Max. Pull Tension:	51.2 lbs (23.2 kg)
Bulk Cable Weight:	45 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor (Not Riser or Plenum), Indoor
Flammability / Reaction to Fire:	VW-1, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Inner Beldfoil« shield over 24 AWG quads. Each quad wrapped in transparent polyester tape. Red Beldfoil« shield over one quad, Green Beldfoil« shield over the other. (2) quads and (2) unshielded conductors cabled.
--------	-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

History

Update and Revision:	Revision Number: 0.359 Revision Date: 12-20-2022
----------------------	--------------------------------------------------

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
8787 060500	Chrome	Reel	500 ft	612825216391	C
8787 060U500	Chrome	UnReel	500 ft	612825216414	

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.