



**Product:** [8677](#)

Electronic, 2 C #16 Str BC, PVC Ins

[Request Sample](#)

## Product Description

Electronic, 2 Conductor 16AWG (19x28) Bare Copper, PVC Insulation

## Technical Specifications

### Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage control (24v, ...); line level audio
------------------------	---

### Construction Details

#### Conductor

Element	Number of Element	Size	Stranding	Material
Conductor(s)	2	16	19x29	BC - Bare Copper

#### Insulation

Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
PVC - Polyvinyl Chloride	0.024 in (0.61 mm)	0.20 in (5.1 mm)	Brown, Red

#### Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.022 in (0.56 mm)	0.149 x 0.254 in

### Electrical Characteristics

#### Electricals

Max. Current
6.5 Amps per Conductor at 25°C

#### Voltage

Voltage Rating
300 V

### Mechanical Characteristics

#### Temperature

UL Temperature	Operating
75°C	-20°C To +75°C

#### Bend Radius

Stationary Min.	Installation Min.
0.38 in (9.7 mm)	0.38 in

Max. Pull Tension:	64.8 lbs (29.4 kg)
Bulk Cable Weight:	33 lbs/1000ft

### Standards and Compliance

European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
--------------------------------	--

APAC Compliance:	China RoHS II (GB/T 26572-2011)
------------------	---------------------------------

## History

Update and Revision:	Revision Number: 0.374 Revision Date: 11-09-2022
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC
8677 060500	Chrome	Reel	500 ft	612825214038

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.