


**Product:** [8723LW](#) 

Audio, Control & Instrument, #22-2pr, PO, Individ. Foil, LSZH Jkt, Cca



REPRESENTATIVE IMAGE

## Product Description

Audio, Control & Instrument Cable, 22 AWG stranded (7x30) tinned copper conductors, polypropylene insulation, twisted pairs, individually Beldfoil® shielded (100% coverage), 24 AWG stranded tinned copper drain wire, LSZH jacket, CPR Cca

## Technical Specifications

### Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; computer communication; panel wiring
------------------------	---

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	No. of Pairs
22	7x30	TC - Tinned Copper	2

Conductor Count:	4
Total Number of Pairs:	2

#### Insulation

Material	Nominal Diameter	Diameter +/- Tolerance
PP - Polypropylene	1.17 mm	0.05 mm

#### Color Chart

Number	Color
Pair 1	Black & Red
Pair 2	Green & White

#### Inner Shield

Type	Material	Material Trade Name	Coverage [%]	Thickness of Foil	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil® (Z-Fold®)	100%	9 µm	TC - Tinned Copper	AWG24/7	7x32

#### Outer Jacket

Material	Nominal Diameter	Nominal Wall Thickness
LSZH - Low Smoke Zero Halogen (Flame Retardant)	5.60 mm	1.1 mm

### Construction and Dimensions

#### Stranding

Twists
8 twist/ft

#### Cabling

Description
2 pairs twisted to cable core

### Electrical Characteristics

#### Conductor DCR

Individual Pair Nominal Shield DCR	Nominal Conductor DCR	Nominal Inner Shield DCR
15 Ohm/1000ft	49.2 Ohm/km	54.5 Ohm/km

#### Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
114.8 pF/m	203.4 pF/m

#### Inductance

Nominal Pair Inductance
0.56 $\mu$ H/m

#### Impedance

Nominal Characteristic Impedance
45 Ohm

#### Delay

Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
66 ns/100m	66%

#### Current

Element	Max. Recommended Current [A]
Conductor(s)	2.3 Amps per Conductor

#### Voltage

Voltage Rating [V]
300 V

### Temperature Range

Installation Temperature Range:	-15°C To +80°C
Storage Temperature Range:	-45°C To +80°C
Operating Temp Range (Flexible Install):	-15°C To +80°C
Operating Temp Range (Fixed Install):	-45°C To +80°C

### Mechanical Characteristics

Oil Resistance:	IEC 60811-404
Max. Pull Tension:	226 N
Min. Bend Radius During Installation:	56 mm
Min. Bend Radius/Minor Axis:	2 in

### Standards

CPR Euroclass:	Cca-s1a,d1,a1
CENELEC Compliance:	EN 50290-2-20

### Applicable Environmental and Other Programs

Environmental Space:	Indoor - Euroclass Cca
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

### Suitability

Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	Yes
Suitability - Sunlight Resistance:	Yes

### Flammability, LS0H, Toxicity Testing

IEC Flammability:	IEC 60332-1-2
IEC 60754-1 - Halogen Amount:	Zero
IEC 60754-2 - Halogen Acid Gas Amount - Max. Conductivity:	2.5 $\mu$ S/mm
IEC 60754-2 - Halogen Acid Gas Amount - Min. pH:	4.3
IEC 61034-2 - Smoke Density Min. Transmittance:	80%

## Related Part Numbers

---

### Variants

Item #	Color	Put-Up Type	Length	EAN
8723LW.00500	Chrome	Reel	500 m	8719605180162

### History

Update and Revision:	Revision Number: 0.55 Revision Date: 02-03-2025
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.