



**Part Number:** 8723NH

Audio, Control & Instrument, #22-2pr, PO, Individ. Foil, LSZH Jkt.

## Product Description

Audio, Control & Instrument Cable, 22 AWG stranded (7x30) tinned copper conductors, polypropylene insulation, twisted pairs, individually Beldfoil® shielded (100% coverage), 24 AWG stranded tinned copper drain wire, LSZH jacket.

## Technical Specifications

### Product Overview

Environmental Space:	Indoor - Euroclass Dca
Suitable Applications:	Instrumentation and computer cable; For data transmission applications

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	No. of Pairs
22	7x30	TC - Tinned Copper	2

Conductor Count:	4
Total Number of Pairs:	2
Conductor Size:	22 AWG

#### Insulation

Material	Nominal Diameter	Diameter +/- Tolerance	Nominal Wall Thickness
PP - Polypropylene	1.17 mm	0.05 mm	0.009 in

#### Color Chart

Number	Color
Pair 1	Black & Red
Pair 2	Green & White

#### Inner Shield Material

Type	Material	Material Trade Name	Coverage [%]	Thickness of Foil	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Aluminum / Polyester	Z-fold®	100 %	9 / 12 µm	Tinned copper	AWG24/7	7x32

#### Outer Shield Material

Material
Unshielded

#### Outer Jacket Material

Material	Color	Nominal Diameter	Nominal Wall Thickness
LSZH / FRNC (UV stabilised)	Chrome (RAL 7037)	4.55 mm	0.65 mm

## Construction and Dimensions

#### Stranding

Twists
8 twist/ft

## Electrical Characteristics

## Conductor DCR

Individual Pair Nominal Shield DCR	Nominal Conductor DCR	Nominal Inner Shield DCR
15 Ohm/1000ft	49.2 Ohm/km	54.5 Ohm/km

## Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
114.8 pF/m	203.4 pF/m

## Inductance

Nominal Inductance	Nominal Pair Inductance
0.17 µH/ft	0.56 µH/m

## Impedance

Nominal Characteristic Impedance
45 Ohm

## Delay

Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
66 ns/100m	66 %

## Current

Element	Max. Recommended Current [A]
Conductor	2.3 A

## Voltage

Voltage Rating [V]
300 V

## Temperature Range

Installation Temp Range:	-15°C To +80°C
Storage Temp Range:	-45°C To +80°C
Operating Temp Range (Flexible Install):	-15°C To +80°C
Operating Temp Range (Fixed Install):	-45°C To +80°C

## Mechanical Characteristics

Oil Resistance:	IEC 60811-404
Bulk Cable Weight:	24 lbs/1000ft
Max Recommended Pulling Tension:	226 N
Min Bend Radius During Installation:	45.5 mm
Min Bend Radius/Minor Axis:	2 in

## Standards

CPR Euroclass:	Dca-s2,d1,a1
CENELEC Compliance:	EN 50290-2-27

## Applicable Environmental and Other Programs

EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-01-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	Yes
Suitability - Sunlight Resistance:	Yes

## Flammability, LS0H, Toxicity Testing

ISO/IEC Flammability:	IEC 60332-1-2 and IEC 60332-3-24
Amount of Halogen acc. to IEC 60754-1 & EN50267-1:	Zero

## Plenum/Non-Plenum

Plenum (Y/N): No

## Part Number

### Variants

Item #	Color	Length
8723NH.001000	Chrome	1,000 m
8723NH.00152	Chrome	152 m
8723NH.00305	Chrome	305 m
8723NH.00500	Chrome	500 m
8723NH.K01000	Chrome	1,000 m
8723NH.K0500	Chrome	500 m
8723NH.01500	Red	500 m

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.