


Product: [8723NH](#) 

Audio, Control & Instrument, #22-2pr, PO, Individ. Foil, LSZH Jkt, Eca



REPRESENTATIVE IMAGE

Product Description

Audio, Control & Instrument Cable, 22 AWG stranded (7x30) tinned copper conductors, polypropylene insulation, twisted pairs, individually Beldfoil® shielded (100% coverage), 24 AWG stranded tinned copper drain wire, LSZH jacket, CPR Dca

Technical Specifications

Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; computer communication; panel wiring
------------------------	---

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
22	7x30	TC - Tinned Copper	2

Conductor Count:	4
Total Number of Pairs:	2

Insulation

Material	Nominal Diameter	Diameter +/- Tolerance	Nominal Wall Thickness
PP - Polypropylene	1.17 mm	0.05 mm	0.009 in

Color Chart

Number	Color
Pair 1	Black & Red
Pair 2	Green & White

Inner Shield Material

Type	Material	Material Trade Name	Coverage [%]	Thickness of Foil	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil® (Z-Fold®)	100%	9 / 12 µm	TC - Tinned Copper	AWG24/7	7x32

Outer Shield Material

Material
No Shield

Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
LSZH - Low Smoke Zero Halogen (Flame Retardant)	4.55 mm	0.65 mm

Construction and Dimensions

Stranding

Twists
8 twist/ft

Electrical Characteristics

Conductor DCR

Individual Pair Nominal Shield DCR	Nominal Conductor DCR	Nominal Inner Shield DCR
15 Ohm/1000ft	49.2 Ohm/km	54.5 Ohm/km

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
114.8 pF/m	203.4 pF/m

Inductance

Nominal Inductance	Nominal Pair Inductance
0.17 μ H/ft	0.56 μ H/m

Impedance

Nominal Characteristic Impedance
45 Ohm

Delay

Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
66 ns/100m	66%

Current

Element	Max. Recommended Current [A]
Conductor	2.3 Amps per Conductor

Voltage

Voltage Rating [V]
300 V

Temperature Range

Installation Temp Range:	-15°C To +80°C
Storage Temp Range:	-45°C To +80°C
Operating Temp Range (Flexible Install):	-15°C To +80°C
Operating Temp Range (Fixed Install):	-45°C To +80°C

Mechanical Characteristics

Oil Resistance:	IEC 60811-404
Bulk Cable Weight:	24 lbs/1000ft
Max. Pull Tension:	226 N
Min Bend Radius During Installation:	45.5 mm
Min Bend Radius/Minor Axis:	2 in

Standards

CPR Euroclass:	Dca-s2,d1,a1
CENELEC Compliance:	EN 50290-2-27

Applicable Environmental and Other Programs

Environmental Space:	Indoor - Euroclass Dca
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-01-01
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LS0H, Toxicity Testing

IEC Flammability:	IEC 60332-1-2 and IEC 60332-3-24
IEC 60754-1 (EN50267-1)- Halogen Amount:	Zero

IEC 60754-2 (EN50267-2)- Halogen Acid Gas Amount - Max. Conductivity:	2.5 µS/mm
IEC 60754-2 (EN50267-2)- Halogen Acid Gas Amount - Min. pH:	4.3
IEC 61034-2 (EN 61034-2) (VDE 0482-1034) - Smoke Density Min. Transmittance:	IEC 61034-2

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Putup Type	Length	EAN
8723NH.00152	Chrome	Reel	152 m	8719605018717
8723NH.00305	Chrome	Reel	305 m	8719605018724
8723NH.00500	Chrome	Reel	500 m	8719605018731
8723NH.001000	Chrome	Reel	1,000 m	8719605018700
8723NH.01500	Red	Reel	500 m	8719605018748

History

Update and Revision:	Revision Number: 0.276 Revision Date: 12-02-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.