



Product: [8723SB](#)

Audio & Instrumentation, 2 Pair 22 AWG, TC, Individually Shielded, Shipboard

### Product Description

Audio & Instrumentation, 22 AWG stranded (7x30) tinned copper conductors, twisted pairs, polypropylene insulation, individually shielded with 100% Beldfoil® shield (100% coverage), 24 AWG stranded tinned copper drain wire, LSZH jacket.

### Technical Specifications

#### Product Overview

Suitable Applications:	shipboard applications; low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; panel wiring
------------------------	---

#### Construction Details

##### Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	2	22 AWG	7x30	TC - Tinned Copper

##### Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PP - Polypropylene	0.009 in (0.23 mm)	0.046 in (1.2 mm)	Black & Red, Green & White

##### Inner Shield

Element	Shield Type	Material	Coverage	Drainwire Type	Notes
Pair(s)	Tape	Bi-Laminate (Alum+Poly)	100%	24 AWG (7x32) TC	foil-out tape on each pair, one drain wire

##### Outer Jacket

Material	Nom. Thickness	Nom. Diameter
LSZH - Low Smoke Zero Halogen (Flame Retardant)	0.034 in (0.86 mm)	0.196 in (4.98 mm)

Overall Cable Diameter (Nominal):	0.196 in (4.98 mm)
-----------------------------------	--------------------

#### Electrical Characteristics

##### Electricals

Element	Nom. Conductor DCR	Nom. Inner Shield DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedance	Nom. Velocity of Prop.	Max. Current
Pair(s)	18.2 Ohm/1000ft	18.38 Ohm/1000ft (60.30 Ohm/km)	35 pF/ft (110 pF/m)	62 pF/ft (200 pF/m)	45 Ohm	66%	2.8 Amps per Conductor at 25°C

##### Voltage

<b>UL Voltage Rating</b>
300 V (CMG-LS)

#### Mechanical Characteristics

##### Temperature

UL Temperature	Operating
105°C	-30°C to +105°C

##### Bend Radius

Stationary Min.	Installation Min.

2.0 in (51 mm)	2.0 in (51 mm)
----------------	----------------

Max. Pull Tension:	42 lbs (19 kg)
--------------------	----------------

Bulk Cable Weight:	24 lbs/1000ft
--------------------	---------------

## Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Non-Halogenated
----------------------------	---

Flammability / Reaction to Fire:	UL 1685 FT4 Loading, IEEE 1202, IEC 60332-1-2, IEC 60332-3-22
----------------------------------	---

CPR Compliance:	CPR Euroclass: Eca
-----------------	--------------------

NEC / UL Compliance:	Article 800, CMG-LS
----------------------	---------------------

CEC / C(UL) Compliance:	CMG-ST1
-------------------------	---------

IEEE Compliance:	Std. 45 Clause 23
------------------	-------------------

European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
--------------------------------	---

UK Regulation Compliance:	UKCA Mark
---------------------------	-----------

APAC Compliance:	China RoHS II (GB/T 26572-2011)
------------------	---------------------------------

## Product Notes

Notes:	UL444, ABS Certificate 20-2049434-PDA
--------	---------------------------------------

## History

Update and Revision:	Revision Number: 0.506 Revision Date: 12-22-2023
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC	Footnote
8723SB 0101000	Black	Reel	1,000 ft	612825214595	C

© 2024 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.