



Product: [8732](#)

Electronic, 2 Pr #22 Str TC, PO Ins, 1Pr w/ TC Brd, PVC Jkt, CM

[Request Sample](#)

Product Description

Electronic, 2 Pair 22AWG (7x30) Tinned Copper, PO Insulation, 1 Pair w/ Tinned Copper Braid(62%) Shield, PVC Outer Jacket, CM

Technical Specifications

Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; computer communication; panel wiring
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Pair(s)	2	22 AWG	7x30	TC - Tinned Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PE - Polyethylene	0.0205 in (0.521 mm)	0.070 in (1.8 mm)	Black, Clear

Inner Shield

Shield Type	Material	Coverage
Braid	Tinned Copper (TC)	62%
No Shield		

Outer Shield

Material
No Shield

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.03 in (0.76 mm)	0.206 x 0.332 in

Overall Cable Diameter (Nominal):	0.206 x 0.332 in
-----------------------------------	------------------

Electrical Characteristics

Electricals

Nom. Conductor DCR	Nom. Inner Shield DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Nom. Characteristic Impedance	Max. Current
18.2 Ohm/1000ft	7.3 Ohm/1000ft (24 Ohm/km)	12 pF/ft (39 pF/m)	21 pF/ft (69 pF/m)	74 Ohm	4.8 Amps per Conductor at 30°C

Voltage

UL Voltage Rating
300 V

Mechanical Characteristics

Temperature

UL Temperature	Operating

60°C	-20°C to +60°C
------	----------------

Bend Radius

Stationary Min.	Installation Min.
0.68 in (17 mm)	0.68 in

Max. Pull Tension:	81 lbs (37 kg)
Bulk Cable Weight:	37 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor
Flammability / Reaction to Fire:	UL 1685 UL Loading, IEC 60332-1-2
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 800, CM
AWM Compliance:	AWM 2094
CEC / C(UL) Compliance:	CM
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

History

Update and Revision:	Revision Number: 0.407 Revision Date: 02-03-2025
----------------------	--

Part Numbers

Variants

Item #	Color	Putup Type	Length	UPC	Footnote
8732 0601000	Chrome	Reel	1,000 ft	612825214762	C

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.