



Product: [89292](#)

Analog Video, RG11, #14 Solid BC, Foil + 65% TC Braid, FEP Jacket, CMP



Product Description

14 AWG solid .064" bare copper conductor, plenum, foam FEP insulation, Duofoil®; tinned copper braid shield (65% coverage), FEP jacket.

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
14	Solid	BC - Bare Copper	0.064 in	1

Conductor Count: 1

Insulation

Material	Nominal Diameter
FEP - Fluorinated Ethylene Propylene (Foam)	0.274 in

Outer Shield

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Tri-Laminate (Alum+Poly+Alum)	Duofoil®	100%
Braid	2	Tinned Copper (TC)		65%

Outer Jacket

Material	Material Trade Name	Nominal Diameter
FEP - Fluorinated Ethylene Propylene	Teflon®	0.346 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR	Conductor Resistance	Nominal Outer Shield DCR	Outer Conductor DCR
2.5 Ohm/1000ft	2.5 Ohm/1000ft		3 Ohm/1000ft	3 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Shield
16.2 pF/ft

Inductance

Nominal Inductance
0.091 µH/ft

Impedance

Nominal Characteristic Impedance
75 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss	Nom. Structural Return Loss (SRL)
1 MHz	0.2 dB/100ft	23 dB
450 MHz	0.4 dB/100ft	

5 MHz	1 dB/100ft	
100 MHz	1.5 dB/100ft	
200 MHz	2.2 dB/100ft	
400 MHz	3.3 dB/100ft	
700 MHz	4.5 dB/100ft	
900 MHz	5.2 dB/100ft	
1000 MHz	5.5 dB/100ft	

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.22 ns/ft	83%

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

Non-UL Temp Rating:	200°C
Operating Temperature Range:	-70°C To +200°C

Mechanical Characteristics

Bulk Cable Weight:	73 lbs/1000ft
Max. Pull Tension:	97 lbs
Min. Bend Radius/Minor Axis:	4 in

Standards

NEC/(UL) Compliance:	CATVP, CMP
CEC/C(UL) Compliance:	CMP
RG Type:	11

Applicable Environmental and Other Programs

Environmental Space:	Indoor - Plenum
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Flammability, LS0H, Toxicity Testing

UL Flammability:	NFPA 262
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

Related Part Numbers

Non-Plenum Number:	9292
--------------------	------

Variants

Item #	Color	Put-Up Type	Length	UPC
89292 010500	Black	Reel	500 ft	612825221456
89292 0101000	Black	Reel	1,000 ft	612825220923

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

Product Notes

Notes:	Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc.
--------	---

History

Update and Revision:	Revision Number: 0.357 Revision Date: 02-03-2025
----------------------	--

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.