



Product: [89696](#)

POS Cable, #22-2pr, BC, FEP, O/A Foil+55% TC Braid, FEP Jkt, CMP

Product Description

Computer POS Cable, 22 AWG solid bare copper conductors, solid FEP insulation, twisted pairs, overall Beldfoil® (100% coverage) + tinned copper braid shield (55% coverage), 22 AWG solid tinned copper drain wire, FEP jacket, plenum rated

Technical Specifications

Product Overview

Suitable Applications:	point of sale; rs-485 applications; extreme high/low temperature environments; computer communication; low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; panel wiring
------------------------	--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
22	Solid	TC - Tinned Copper	2

Conductor Count: 4

Insulation

Material	Material Trade Name
FEP - Fluorinated Ethylene Propylene	Teflon®

Color Chart

Number	Color
1	Blue & White with Blue Stripe
2	Orange & White with Orange Stripe

Outer Shield

Type	Layer	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	1	Bi-Laminate (Alum+Poly)	Beldfoil®	100%	TC - Tinned Copper	22	Solid
Braid	2	Tinned Copper (TC)		55%			

Table Notes: Polyester Tape

Outer Jacket

Material	Material Trade Name	Nominal Diameter
FEP - Fluorinated Ethylene Propylene	Teflon®	0.262 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
16.5 Ohm/1000ft	4.2 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
15.5 pF/ft	27 pF/ft

Inductance

Nominal Inductance

0.15 µH/ft

Impedance**Nominal Characteristic Impedance**

100 Ohm

Delay

Max. Delay Skew	Nominal Delay	Nominal Velocity of Propagation (VP) [%]
69.5 ns/100m	1.46 ns/ft	70%

High Frequency**Frequency [MHz]**

0.3 MHz
0.6 MHz
1 MHz
1.5 MHz

Voltage**UL Voltage Rating**

300 V RMS

Temperature Range

Operating Temperature Range: -70°C To +200°C

Mechanical Characteristics

Bulk Cable Weight:	41.1 lbs/1000ft
Max. Pull Tension:	65 lbs
Min. Bend Radius/Minor Axis:	5.5 in

Standards

NEC/(UL) Compliance:	CMP
CEC/C(UL) Compliance:	CMP

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
MII Order #39 (China RoHS):	Yes

Flammability, LSOH, Toxicity Testing

UL Flammability:	NFPA 262 Plenum Flame Test (UL910)
UL voltage rating:	300 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	Yes
---------------	-----

Related Part Numbers

Non-Plenum Number:	9696
--------------------	------

Variants

Item #	Color	UPC
89696 0101000	Black	612825221081

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

Product Notes

Notes:	Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc.
--------	---------------------------------------------------------------------------------------------------------

History

Update and Revision:	Revision Number: 0.339 Revision Date: 02-03-2025
----------------------	--------------------------------------------------

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.