



**Product:** [8770NH](#)

Electronic, 3C #18 Str TC, PO ins, OS, LSNH Jkt 300V, Cca

## Product Description

Electronic, 3 Conductor AWG 18 Tinned Copper - Stranded, Polyolefin (PO, PE, PP) insulation, Foil(s) or Copper Tape(s) shielding, LSZH / FRNC jacket , 300V, Cca

## Technical Specifications

### Product Overview

Suitable Applications:	Audio, Control & Instrumentation cable; For data transmission applications
------------------------	--

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	No. of Conductors
18	16x30	TC - Tinned Copper	3

Conductor Count:	3
------------------	---

#### Insulation

Material	Nominal Diameter	Diameter +/- Tolerance	Nominal Wall Thickness
PE - Polyethylene	2.08 mm	0.05 mm	0.018 in

#### Color Chart

Number	Color
Wire 1	Black
Wire 2	Red
Wire 3	Clear

#### Outer Shield Material

Type	Material	Material Trade Name	Coverage [%]	Thickness of Foil	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil® (Z-Fold®)	100%	9 / 12 µm	TC - Tinned Copper	AWG20/7	Stranded

#### Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
LSZH - Low Smoke Zero Halogen (Flame Retardant)	6.25 mm	0.84 mm

## Construction and Dimensions

#### Cabling

Description	Twists
3 wires twisted to cable core	8 twist/ft

## Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
21.7 Ohm/km	27.9 Ohm/km

#### Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield
78.7 pF/m	157.5 pF/m

#### Inductance

Nominal Inductance
0.605 µH/m

#### Impedance

Nominal Characteristic Impedance
69 Ohm

#### Delay

Nominal Velocity of Propagation (VP) [%]
66%

#### Current

Element	Max. Recommended Current [A]
Conductor	5.3 Amps per Conductor

#### Voltage

Voltage Rating [V]
300 V

### Temperature Range

Installation Temp Range:	-15°C To +80°C
Storage Temp Range:	-45°C To +80°C
Operating Temp Range (Flexible Install):	-15°C To +80°C
Operating Temp Range (Fixed Install):	-45°C To +80°C

### Mechanical Characteristics

Oil Resistance:	IEC 60811-404
Bulk Cable Weight:	38 lbs/1000ft
Max. Pull Tension:	335 N
Min Bend Radius During Installation:	62.5 mm
Min Bend Radius/Minor Axis:	2.5 in

### Standards

NEC/(UL) Compliance:	CMG
CEC/C(UL) Compliance:	CMG
CPR Euroclass:	Cca-s1,d1,a1
CENELEC Compliance:	EN 50290-2-27

### Applicable Environmental and Other Programs

Environmental Space:	Indoor - Euroclass Cca
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-11-14
MII Order #39 (China RoHS):	Yes

### Suitability

Suitability - Indoor:	Yes
Suitability - Non-Halogenated:	Yes
Suitability - Sunlight Resistance:	Yes

### Flammability, LSOH, Toxicity Testing

IEC Flammability:	IEC 60332-1-2 and IEC 60332-3-24
IEC 60754-1 (EN50267-1)- Halogen Amount:	Zero
IEC 60754-2 (EN50267-2)- Halogen Acid Gas Amount - Max. Conductivity:	2.5 µS/mm
IEC 60754-2 (EN50267-2)- Halogen Acid Gas Amount - Min. pH:	4.3
IEC 61034-2 (EN 61034-2) (VDE 0482-1034) - Smoke Density Min. Transmittance:	60%

UL voltage rating:	300 V RMS (UL AWM Style 2093)
--------------------	-------------------------------

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Part Number

### Variants

Item #	Color	Putup Type	Length	EAN
8770NH.00305	Chrome	Reel	305 m	8719605019240

## History

Update and Revision:	Revision Number: 0.261 Revision Date: 01-08-2021
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.