



Product: [8G1.0SY](#) 

MachFlex™ 350 SY, 7 C + 1 G 1.0 mm² Str BC, PVC Ins, PVC Inner Jkt, GSW Brd, PVC Outer Jkt

Product Description

MachFlex™ 350 SY VDE Certified Control Cable 7 Conductor + 1 Ground 1.0mm² Bare Copper, PVC Insulation, PVC Inner Jacket, Galvanized Steel Wire Braiding Armor, PVC Outer Jacket

Technical Specifications

Product Overview

Suitable Applications:	Application for occasional flexing or fixed installation connecting precision control sensors, multi axis control machines, temperature controllers, control panels, machine cutting tools, auxiliary equipment, motor speed control, production machinery and many more in harsh industrial environment.
------------------------	---

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Stranding Class	Material
Conductor(s)	7	1 mm ²	Stranded	Class 5	BC - Bare Copper
Ground	1	1 mm ²	Stranded	Class 5	BC - Bare Copper

Insulation

Material	Nom. Insulation Diameter	Color Code
PVC - Polyvinyl Chloride	2.06 mm (0.0811 in)	Black #1, Black #2, Black #3, Black #4, Black #5, Black #6, Black #7
PVC - Polyvinyl Chloride		Yellow with Green strip

Inner Jacket

Separator	Material	Nom. Diameter
non-Woven Tape	PVC - Polyvinyl Chloride	8.8 mm (0.35 in)

Armor

Armor Type & Material	Armor Material Diameter
SWB - Steel Wire Braid Armor	9.7 mm (0.38 in)

Outer Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	12 mm (0.47 in)

Electrical Characteristics

Electricals

Nom. Conductor DCR
19.5 Ohm/km (5.94 Ohm/1000ft)

Voltage

Voltage Rating
300 / 500 V

Mechanical Characteristics

Temperature

Operating	Installation

-15°C to +70°C (Occasional movement) -40°C to +80°C(Fixed installation)

Bend Radius

Installation Min.	Flexing Min.
72 mm (2.8 in)	240 mm (9.4 in)

Bulk Cable Weight: 212 kg/km (142 lbs/1000ft)

Standards and Compliance

Environmental Suitability:	UV Resistance, Oil Resistance
Flammability / Reaction to Fire:	IEC 60332-1-2
ISO/IEC Compliance:	IEC 60228
CENELEC Compliance:	EN 50290-2-22
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU (RoHS 2 amendment), EU Directive 2011/65/EU (RoHS 2)
APAC Compliance:	China RoHS II (GB/T 26572-2011)
Other Standard Compliance(s):	IEC 60227-5, EN 50525-2-51

Product Notes

Notes: Conductor Standards : DIN VDE 0295, BS 6360 Cable Standards : VDE 0281-13, VDE Certification No. 40041970, VDE Registration No. 8770. EMEA PN : 8GCSY

History

Update and Revision: Revision Number: 0.31 Revision Date: 03-19-2024

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.