



Product: [8P0.5YCY](#)

MachFlex™ LiYCY(TP), 8 Pr 0.5mm² Str BC, PVC Ins, TCBS, PVC Jkt

Product Description

MachFlex™ LiYCY(TP) Control VDE Certified & Twisted Pair PVC Signal Cables 8 Pair 0.5mm² Stranded Bare Copper, PVC Insulation, Tinned Copper Braid Shield, PVC Jacket

Technical Specifications

Product Overview

Suitable Applications:	Designed for applications which are installed in occasional flexing and fixed locations. Cable applications include precision control sensors, pressure gauge, temperature controllers, control panels, vibration monitoring systems, intelligent security controllers, production machinery and many more. Tinned copper braid shield ensure the cables with excellent noise immunity. Twisted pair (TP) design reduced crosstalk effects
------------------------	--

Construction Details

Conductor

Element	Size	Stranding	Material
Conductor(s)	0.5 mm ²	Stranded	BC - Bare Copper

Insulation

Material	Color Code
PVC - Polyvinyl Chloride	White, Brown, Green, Yellow, Gray, Pink, Blue, Red, Black, Violet, Gray with Pink strips, Red with Blue strips, White with Green strips, Brown with Green strips, White with Yellow strips, Yellow with Brown strips

Outer Shield

Shield Type	Material
Braid	Tinned Copper (TC)

Outer Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	12.4 mm (0.488 in)

Electrical Characteristics

Electricals

Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Shield
120 pF/m (37 pF/ft)	160 pF/m (49 pF/ft)

Voltage

Voltage Rating
500 V (Max. Operating Voltage), 1500 V (Testing Voltage)

Mechanical Characteristics

Temperature

Operating
5°C to +70°C

Bend Radius

Installation Min.

74.4 mm (2.93 in)

Bulk Cable Weight: 199 kg/km (134 lbs/1000ft)

Standards and Compliance

Environmental Suitability:	Indoor, Outdoor, Sunlight Resistance, UV Resistance
Flammability / Reaction to Fire:	IEC 60332-1-2, DIN VDE 0482-332-1-2, DIN EN 60332-1-2
ISO/IEC Compliance:	IEC 60228
CENELEC Compliance:	EN 50290-2-22EN 50363-4-1
Other Standard Compliance(s):	VDE 0812, DIN 47100, BS 6360

History

Update and Revision: Revision Number: 0.33 Revision Date: 06-29-2023

© 2023 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.