


**Product:** [8786](#) 



Audio, Control and Instrumentation, 4 Conductor 24 AWG, Shielded; 2 Conductor 22 AWG Unshielded, CM

## Product Description

4 Conductor 24 AWG stranded (7x32) and 2 Conductor 22 AWG stranded (7x30) TC conductors, PVC insulation, (4) conductors cabled, 22 AWG stranded TC drain wire, CM PVC jacket.

## Technical Specifications

### Product Overview

Suitable Applications:	low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; computer communication; panel wiring
------------------------	---

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Conductors
24	7x32	TC - Tinned Copper	0.024 in	4
22		TC - Tinned Copper	0.03 in	2

Conductor Count:	6
------------------	---

#### Insulation

Material	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.015 in

#### Color Chart

Number	Color
1	Blue Quad
2	Blue
3	White

#### Color Chart 2

Color
Black, Green, Red, Yellow
Blue Beldfoil®
Blue, White
Unshielded

#### Inner Shield Material

Type	Material	Material Trade Name	Coverage [%]	Drainwire Material	Drainwire AWG	Drainwire Construction n x D
Tape	Bi-Laminate (Alum+Poly)	Beldfoil® (Z-Fold®)	100%		22	7x30
			100%	TC - Tinned Copper		

#### Outer Shield Material

Material
No Shield

#### Outer Jacket Material

Material	Nominal Diameter	Nominal Wall Thickness
PVC - Polyvinyl Chloride	0.236 in	0.028 in

## Electrical Characteristics

### Conductor DCR

Element	Nominal Conductor DCR	Nominal Inner Shield DCR
24 AWG	23.9 Ohm/1000ft	11.9 Ohm/1000ft
	15 Ohm/1000ft	
24 AWG Quad		

### Capacitance

Nom. Capacitance Between Conductors in Quad
20 pF/ft

### Current

Max. Recommended Current [A]
1.5 Amps per Conductor at 25°C (24 AWG)
2 Amps per Conductor at 25°C (22 AWG)

### Voltage

UL Voltage Rating
300 V RMS

Electrical Characteristics Notes:	2/c 21 AWG equivalent DCR when connected to a 3-pin XLR
-----------------------------------	---

## Temperature Range

Non-UL Temp Rating:	90°C
Operating Temp Range:	-20°C To +90°C

## Mechanical Characteristics

Bulk Cable Weight:	30 lbs/1000ft
Max. Pull Tension:	40.2 lbs
Min Bend Radius/Minor Axis:	2.5 in

## Standards

NEC Articles:	Article 800
NEC/(UL) Compliance:	CM
CEC/C(UL) Compliance:	CM

## Applicable Environmental and Other Programs

Environmental Space:	Indoor (Not Riser or Plenum)
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU (RoHS 2 amendment):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Indoor:	Yes
-----------------------	-----

## Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1685 UL Loading
UL voltage rating:	300 V RMS

## Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Part Number

### Variants

Item #	Color	Putup Type	Length	UPC
8786 060500	Chrome	Reel	500 ft	612825216377
8786 060U500	Chrome	UnReel	500 ft	612825216407

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

## Product Notes

Notes:	Inner Beldfoil« shield over 24 AWG quads. (4) conductors cabled under 100% Beldfoil« shield; (2) conductors unshielded. Quad connection scheme: The black & red wires (or wires directly opposite one another) are connected together to form one conductor, and similarly the green & yellow wires (or remaining wires) are connected together to form the second conductor.
--------	---

## History

Update and Revision:	Revision Number: 0.276 Revision Date: 03-16-2021
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.