




Product: [902007](#) 

XTRAGUARD FLEX, 7C #20, Str, PVC/NYLON, 600 V, AWM/STYLE 1316 90C, AWM/STYLE 20626 90C, SUN RES, OIL RES I/II, PLTC 90C, CSA C(RU) AWM I/II A/B, CSA FT4

Product Description

XTRAGUARD FLEX, 7 Conductor 20 AWG (10/30) BC - Bare Copper, PVC/NYLON Insulation, Slate TPE Outer Jacket, AWM/STYLE 1316 90C, AWM/STYLE 20626 90C, SUN RES, OIL RES I/II, PLTC 90C, CSA C(RU) AWM I/II A/B, CSA FT4 C(RU) AWM I/II A/B, FT4 UL FT4; CSA FT4

Technical Specifications

Product Overview

Suitable Applications:	Data, communication, audio, and low-level signal transmission; industrial networking, serial communication, control panels, automation equipment, and instrumentation systems.
------------------------	--

Construction Details

Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	7	20 AWG	10x30	BC - Bare Copper

Insulation

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Conductor(s)	PVC/Nylon - Polyvinyl Chloride + Nylon	0.016 in (0.41 mm)	0.079 in (2.0 mm)	Green/Yellow, Black#1, Black#2, Black#3, Black#4, Black#5, Black#6

Outer Jacket

Material	Nom. Thickness	Nom. Diameter
TPE - Thermoplastic Elastomer	0.045 in (1.1 mm)	0.343 in (8.71 mm)

Overall Cable Diameter (Nominal): 0.343 in (8.71 mm)

Electrical Characteristics

Electricals

Element	Nom. Capacitance Cond-to-Cond	Nom. Inductance
Conductor(s)	23.6 pF/ft (77.4 pF/m)	0.21 μ H/ft (0.69 μ H/m)

Voltage

UL Voltage Rating	Voltage Rating
600 V (AWM 20626)	600 V (CSA AWM)

Mechanical Characteristics

Temperature

UL Temperature	Operating	Installation
90°C	-30°C To +90°C	-5°C To +90°C

Bend Radius

Stationary Min.	Installation Min.
1.4 in (36 mm)	2.1 in (53 mm)

Max. Pull Tension: 16.5 lbs (7.48 kg)

Standards and Compliance

Environmental Suitability: Indoor, Outdoor, Sunlight Resistance, Oil Resistance

Sustainability:	CA Prop 65
Flammability / Reaction to Fire:	UL1685 FT4 Loading, FT4
NEC / UL Compliance:	Article 725, PLTC
AWM Compliance:	AWM 20626, AWM I/II A/B
European Directive Compliance:	EU Directive 2015/863/EU (RoHS 2 amendment), REACH, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Alpha Wire -* P/N 902007 7C 20 AWG (UL) TYPE PLTC 90C OIL RES I/II SUN RES OR RU AWM STYLE 20626 90C 600V OR CRU AWM I/II A/B 90C 600V FT4 CE ROHS (DATE CODE) (SEQ FOOTAGE)
--------	--

History

Update and Revision:	Revision Number: 0.19 Revision Date: 06-30-2026
----------------------	---

Part Numbers

Variants

Item #	Color	Putup Type	Length
902007 SL005	Green/Yellow	Reel	100 ft

© 2026 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.