



Product: [8810](#)

Speaker Cable, 2 Conductor 10 AWG BC, Unshielded, CM



## Product Description

2 Conductor 10 AWG, stranded (19x23) bare copper conductors, PVC/Nylon insulation, PVC jacket.

## Technical Specifications

### Product Overview

Suitable Applications:	AUDITORIUM , STADIUM , RACE TRACK , CHURCH , TEMPLE , SYNAGOGUE , PLACE OF ASSEMBLY , CASINO , SOUND
------------------------	--

### Construction Details

#### Conductor

Element	No. of Elements	Size	Stranding	Material
Conductor(s)	2	10	19x23	BC - Bare Copper

#### Insulation

Element	Material
Conductor(s)	PVC - Polyvinyl Chloride
	Nylon

#### Outer Shield

Material
No Shield

#### Outer Jacket

Material	Nom. Diameter
PVC - Polyvinyl Chloride	0.424 in (10.8 mm)

### Electrical Characteristics

#### Electricals

Element	Nom. Conductor DCR	Max. Current
Conductor(s)	1 Ohm/1000ft	16 Amps per Conductor at 25°C

#### Voltage

UL Voltage Rating
600 V

### Mechanical Characteristics

#### Temperature

UL Temperature	Operating
75°C Wet; 90°C Dry	-30°C To +75°C Wet; -30°C To +90°C Dry

Max. Pull Tension:	234 lbs (106 kg)
Bulk Cable Weight:	104 lbs/1000ft

### Standards and Compliance

Environmental Suitability:	Indoor/Outdoor, Indoor, Outdoor, Sunlight Resistance, Burial
Flammability / Reaction to Fire:	UL 1685 FT4 Loading, IEEE 1202 FT4
CPR Compliance:	CPR Euroclass: Eca
NEC / UL Compliance:	Article 336, Article 760, NPLF, TC, THHN/THWN Singles
European Directive Compliance:	EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
UK Regulation Compliance:	UKCA Mark

## History

Update and Revision:	Revision Number: 0.407 Revision Date: 02-03-2025
----------------------	--

## Part Numbers

### Variants

Item #	Color	Putup Type	Length	UPC	Footnote
8810 0101000	Black	Reel	1,000 ft	612825216629	C

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.