



Product: [8818WB](#)

Speaker Cable, 2 Conductor 18 AWG BC, Unshielded, Waterblocked

Product Description

2 Conductor 18 AWG stranded (19x30) bare copper conductors, PVC/Nylon insulation, PVC jacket.

Technical Specifications

Product Overview

Suitable Applications:	AUDITORIUM , STADIUM , RACE TRACK , CHURCH , TEMPLE , SYNAGOGUE , PLACE OF ASSEMBLY , CASINO , SOUND
------------------------	--

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Conductors
18	19x30	BC - Bare Copper	2

Conductor Count:	2
------------------	---

Insulation

Layer	Material
1	PVC - Polyvinyl Chloride
2	Nylon

Color Chart

Number	Color
1	Black
2	White

Outer Shield

Material
No Shield

Outer Jacket

Material	Nominal Diameter	Separator Material
PVC - Polyvinyl Chloride	0.309 in	Waterblocking Tape

Construction and Dimensions

Cabling

Filler
Waterblocking Tape Separator Material

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR
6.6 Ohm/1000ft

Voltage

UL Voltage Rating

600 V

Temperature Range

Operating Temperature Range:	-30°C To +75°C Wet; -30°C To +90°C Dry
Wet Temp Range:	-30°C To +75 °C
Dry Temp Range:	-30°C To +90°C Dry

Mechanical Characteristics

Bulk Cable Weight:	47 lbs/1000ft
Max. Pull Tension:	94 lbs
Min. Bend Radius/Minor Axis:	3.1 in

Standards

NEC/(UL) Compliance:	NPLF, TC, TFFN
----------------------	----------------

Applicable Environmental and Other Programs

Environmental Space:	Indoor/Outdoor
EU Directive 2011/65/EU (RoHS 2):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2002/96/EC (WEEE)

Suitability

Suitability - Burial:	Yes
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LS0H, Toxicity Testing

UL Flammability:	UL1581 Vertical Tray
CSA Flammability:	FT4
IEEE Flammability:	1202
UL voltage rating:	600 V RMS

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Related Part Numbers

Variants

Item #	Color	Put-Up Type	Length
8818WB 0101000	Black	Reel	1,000 ft

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

History

Update and Revision:	Revision Number: 0.38 Revision Date: 05-31-2024
----------------------	---

© 2025 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.