

**Part Number: 88240**

53 Ohm, RG58, 20 AWG, CMP



**Product Description**

RG-58/U type, 20 AWG solid .033" bare copper conductor, plenum, FEP Teflon® insulation, tinned copper braid shield (95% coverage), FEP Teflon® jacket.

**Technical Specifications**

**Product Overview**

Environmental Space:	Indoor
----------------------	--------

**Physical Characteristics (Overall)**

**Conductor**

AWG	Stranding	Material	Nominal Diameter	No. of Coax
20	Solid	BC - Bare Copper	0.032 in	1

Conductor Count:	1
------------------	---

**Insulation**

Material	Material Trade Name	Nominal Diameter
FEP - Fluorinated Ethylene Propylene	Teflon®	0.107 in

**Outer Shield Material**

Type	Material	Coverage [%]
Braid	TC - Tinned Copper	95 %

**Outer Jacket Material**

Material	Material Trade Name	Nominal Diameter
FEP - Fluorinated Ethylene Propylene	Teflon®	0.159 in

**Electrical Characteristics**

**Conductor DCR**

Nominal Conductor DCR	Nominal Outer Shield DCR	Outer Conductor DCR
10.2 Ohm/1000ft	6.7 Ohm/1000ft	6.7 Ohm/1000ft

**Capacitance**

Nom. Capacitance Conductor to Shield
26.4 pF/ft

**Inductance**

Nominal Inductance
0.088 µH/ft

**Impedance**

Nominal Characteristic Impedance
53 Ohm

**High Frequency (Nominal/Typical)**

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.5 dB/100ft
10 MHz	1.2 dB/100ft
50 MHz	3 dB/100ft
100 MHz	4.3 dB/100ft
200 MHz	6.4 dB/100ft
400 MHz	9.7 dB/100ft
700 MHz	13.7 dB/100ft
900 MHz	16.1 dB/100ft
1000 MHz	17.3 dB/100ft

## Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.48 ns/ft	69.5 %

## Power Rating

Frequency [MHz]	Max. Power Rating [W]	Nominal Power Rating [W]
1 MHz	4,798.7 W	4,798.7 W
10 MHz	1,937.2 W	1,937.2 W
50 MHz	782.4 W	782.4 W
100 MHz	542.2 W	542.2 W
200 MHz	370.3 W	370.3 W
400 MHz	248.5 W	248.5 W
700 MHz	177.7 W	177.7 W
900 MHz	153.0 W	153 W
1,000 MHz	143.2 W	143.2 W

## Voltage

Non-UL Voltage Rating	UL Voltage Rating
1400V RMS	300V RMS

## Temperature Range

UL Temp Rating:	200°C
Operating Temp Range:	-70°C To +200°C

## Mechanical Characteristics

Bulk Cable Weight:	24 lbs/1000ft
Max Recommended Pulling Tension:	47 lbs
Min Bend Radius/Minor Axis:	1.5 in

## Standards

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
RG Type:	RG-58/U Type

## Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	No
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

## Suitability

Suitability - Aerial:	Yes - When supported by messenger wire
Suitability - Burial:	Yes
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Sunlight Resistance:	No

### Flammability, LS0H, Toxicity Testing

UL Flammability:	NFPA 262
CSA Flammability:	FT6

### Part Number

Plenum (Y/N):	Yes
Plenum Number:	8240

### Variants

Item #	Color
88240 0101000	BLACK
88240 010500	BLACK

### Product Notes

Notes:	Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc.
--------	---

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS(Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be instock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.