



**Product:** [8888](#)

Portable Cordage, 2 C #18 Str BC, PVC Ins, UL Type SPT-1

[Request Sample](#)

**Product Description**

Electronic, 2 Conductor 18AWG (42x34) Bare Copper, PVC Insulation, Portable Cordage SPT-1

**Technical Specifications**

**Construction Details**

**Conductor**

Element	Number of Element	Size	Stranding	Material
Pair(s)	2	18 AWG	42x34	BC - Bare Copper

**Insulation**

Element	Material	Nom. Thickness	Nom. Insulation Diameter	Color Code
Pair(s)	PVC - Polyvinyl Chloride	0.032 in (0.81 mm)	0.11 x 0.207 in mm	Brown

**Outer Shield**

Material
No Shield

**Electrical Characteristics**

**Electricals**

Nom. Conductor DCR	Max. Current
4.17 Ohm/1000ft	15 Amps per Conductor at 25°C (7 Amps over 50 ft)
	7 Amps per Conductor at 25°C

**Voltage**

UL Voltage Rating
300 V

**Mechanical Characteristics**

**Temperature**

UL Temperature
60°C

**Bend Radius**

Stationary Min.	Installation Min.
1.1 in (28 mm)	1.1 in

Max. Pull Tension:	41 lbs
Bulk Cable Weight:	20 lbs/1000ft

**Standards and Compliance**

NEC / UL Compliance:	Article 400, SPT-1
European Directive Compliance:	EU CE Mark, EU Directive 2011/65/EU (RoHS 2), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

## History

Update and Revision:	Revision Number: 0.287 Revision Date: 12-23-2021
----------------------	--

## Variants

Item #	Color	Putup Type	Length	UPC
8888 001250	Brown	Reel	250 ft	612825217503
8888 001U1000	Brown	Reel	1,000 ft	612825217497

© 2022 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.