

Product: [9141](#) 

Precision Video Coax, RG59, #20 Solid BC, Double 98% TC/BC Braid



Product Description

20 AWG solid .031" bare copper conductor, polyethylene insulation, tinned copper/bare copper braid shield (98% coverage), polyethylene jacket.

Technical Specifications

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
20	Solid	BC - Bare Copper	0.031 in	1

Conductor Count:

Insulation

Material	Nominal Diameter
PE - Polyethylene	0.2 in

Outer Shield Material

Type	Layer	Material	Coverage [%]
Braid	1	Tinned Copper (TC)	98%
Braid	2	Tinned Copper (TC)	98%

Outer Jacket Material

Material	Nominal Diameter
PE - Polyethylene	0.305 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance	Nominal Outer Shield DCR	Outer Conductor DCR
9.9 Ohm/1000ft	9.9 Ohm/1000ft	1.1 Ohm/1000ft	1.1 Ohm/1000ft

Capacitance

Nom. Capacitance Conductor to Shield
20 pF/ft

Impedance

Nominal Characteristic Impedance
75 Ohm

Return Loss (RL)

Frequency [MHz]	Minimum Return (RL)
5-216 MHz	27 dB
217-850 MHz	23 dB

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
-----------------	---------------------

1 MHz	0.3 dB/100ft
3.6 MHz	0.5 dB/100ft
10 MHz	0.8 dB/100ft
71.5 MHz	2 dB/100ft
135 MHz	3.5 dB/100ft
270 MHz	4.3 dB/100ft
360 MHz	5 dB/100ft
540 MHz	6.2 dB/100ft
720 MHz	7.2 dB/100ft
750 MHz	7.4 dB/100ft
1000 MHz	9.1 dB/100ft

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.54 ns/ft	66%

Voltage

Non-UL Voltage Rating
1700 V RMS

Temperature Range

Non-UL Temp Rating:	80°C
Operating Temp Range:	-55°C To +80°C

Mechanical Characteristics

Bulk Cable Weight:	68 lbs/1000ft
Max. Pull Tension:	172 lbs
Min Bend Radius/Minor Axis:	3 in

Standards

RG Type:	59/U Type
Series Type:	59

Applicable Environmental and Other Programs

Environmental Space:	Indoor/Outdoor
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	No
EU RoHS Compliance Date (yyyy-mm-dd):	2004-01-01
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Aerial:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	No

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Part Number

Variants

Item #	Color	Putup Type	Length	UPC
9141 3681000	Clear, Transparent	Reel	1,000 ft	612825224730

Footnote: C - CRATE REEL PUT-UP.

Product Notes

Notes:	Dielectric Strength: 8 kV.
--------	----------------------------

History

Update and Revision:	Revision Number: 0.269 Revision Date: 09-30-2020
----------------------	--

© 2020 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.