

**Part Number: 89207**

100Ω Twinax, #20-1c TC/1c BC, FEP, Dufoil® TC Braid, FEP Jkt, CMP



## Product Description

100 Ohm Twinax, 20 AWG stranded (7x28) one tinned, one bare copper conductor, FEP insulation, overall FEP dielectric, Dufoil® + tinned copper braid shield 85%, FEP jacket.

## Technical Specifications

### Physical Characteristics (Overall)

#### Conductor

AWG	Stranding	Material	Construction n x D	Nominal Diameter	No. of Conductors	No. of Pairs
20	7x28	TC - Tinned Copper	Stranded	0.037 in	1	1
	7x28 AWG	BC - Bare Copper	Stranded	0.037 in	1	

Conductor Count:	2
AWG Size:	20

#### Insulation

Material	Material Trade Name	Nominal Diameter
FEP - Fluorinated Ethylene Propylene	Teflon®	0.072 in

#### Color Chart

Number	Color
1	Natural (bare conductor)
2	Natural (tinned conductor)

#### Inner Jacket Material

Material	Material Trade Name	Nominal Diameter
FEP - Fluorinated Ethylene Propylene	Teflon®	0.201 in

#### Outer Shield Material

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Aluminum Foil-Polyester Tape-Aluminum Foil	Dufoil®	100 %
Braid	2	TC - Tinned Copper		85 %

#### Outer Jacket Material

Material	Material Trade Name	Nominal Diameter
FEP - Fluorinated Ethylene Propylene	Teflon®	0.259 in

### Electrical Characteristics

#### Conductor DCR

Nominal Conductor DCR	Nominal Outer Shield DCR
9.5 Ohm/1000ft	2.5 Ohm/1000ft

#### Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Other Conductor to Shield	Nom. Capacitance Conductor to Shield
14 pF/ft	23 pF/ft	14 pF/ft

#### Inductance

Nominal Inductance
--------------------

0.155 µH/ft

#### Impedance

##### Nominal Characteristic Impedance

100 Ohm

#### High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.3 dB/100m
10 MHz	1.2 dB/100m
50 MHz	2.8 dB/100m
100 MHz	4.1 dB/100m
200 MHz	6.4 dB/100m
300 MHz	8.4 dB/100m
400 MHz	10.2 dB/100m

#### Delay

Max. Delay Skew	Nominal Delay	Nominal Velocity of Propagation (VP) [%]
69.5 ns/100m	1.46 ns/ft	69.50 %

#### Voltage

##### UL Voltage Rating

300V RMS

#### Temperature Range

Operating Temp Range:	-70°C To +200°C
-----------------------	-----------------

#### Mechanical Characteristics

UV Resistance:	Yes - Black only
Bulk Cable Weight:	52 lbs/1000ft
Max Recommended Pulling Tension:	88 lbs
Min Bend Radius/Minor Axis:	2.75 in

#### Standards

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
CPR Euroclass:	Eca

#### Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/96/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2011/65/EU (ROHS II)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2001-01-01

#### Suitability

Suitability - Aerial:	Yes - Black only, when supported by messenger wire
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes - Black only

#### Flammability, LS0H, Toxicity Testing

UL Flammability:	NFPA 262
CSA Flammability:	FT6

#### Part Number

Plenum (Y/N):	Yes
Non-Plenum Number:	9207

#### Variants

Item #	Color	Footnote
89207 010100	BLACK	C
89207 0101000	BLACK	C
89207 010500	BLACK	C

Footnote:	C - CRATE REEL PUT-UP.
-----------	------------------------

#### Product Notes

Notes:	Teflon® is a registered trademark of Chemours and is used under license by Belden, Inc.
--------	---

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS(Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.